



Sturdy and Reliable versatile lighting solution

EnduraLED Bulkhead

EnduraLED Bulkhead luminaire is a sustainable and reliable offering for indoor or semi-outdoor public area with IP66 ingress protection. The product offers two lumen packs with two different CCT's and suitable for versatile applications such as staircases, industrial areas, circulation areas, lift wells etc. Pressure die cast housing and high impact resistance polycarbonate cover make this bulkhead maintenance free solution for heavy duty industries.

Benefits

- Sturdy design that combines well with industrial applications
- Higher life class with minimal maintenance
- Best in class efficacy ensures lower ROI
- Easy installation with standard tools
- Ensures visual comfort and reduces eye strain through diffused natural lighting

Features

- High ingress protection-IP66
- Impact resistant-IK09
- Compact integral design
- Color temperature - 4000K / 6500K and Lumen packs - 700 lm /1100 lm
- Pressure diecast housing with robust polycarbonate cover
- External mounting through simple tools
- Long lifetime: 50000 Hrs.

EnduraLED Bulkhead


Application

- Lift wells
- Heavy duty industries
- Indoor circulation areas
- Balconies and terraces semi outdoor area
- Government buildings

Warnings and Safety

- Meant for Indoor Industrial Application Only.

Dimensional drawing



EnduraLED Bulkhead

General Information

Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Beam angle of light source	120 degree(s)
Optical cover type	Polycarbonate
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	110 lm/W
Optic type	Beam angle 120°

Operating and Electrical

Input Voltage	140-270 V
---------------	-----------

Temperature

Ambient temperature range	0 to +45 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Gray
---------------	------

Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK09
Ingress protection code	IP66

Initial Performance (IEC Compliant)

Initial chromaticity	<5
----------------------	----

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
919515813250	WT202W LED10S CW PSU S3 PC	6500 K	1,100 lm
919515813251	WT202W LED10S NW PSU S3 PC	4000 K	1,100 lm
919515813252	WT202W LED6S CW PSU S3 PC	6500 K	700 lm
919515813253	WT202W LED6S NW PSU S3 PC	4000 K	700 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
919515813250	WT202W LED10S CW PSU S3 PC	10 W
919515813251	WT202W LED10S NW PSU S3 PC	10 W

Order Code	Full Product Name	Power Consumption
919515813252	WT202W LED6S CW PSU S3 PC	6 W
919515813253	WT202W LED6S NW PSU S3 PC	6 W

