



Slim with high efficacy

GreenPerform Panel

GreenPerform Panel RC160 is a slim Panel with high efficacy in the market. It offers two lumen options with four dimension types, 200X1200, 300X1200, 600x600, 600x1200, and three mounting options, recessed, suspended and plaster ceiling. It also offers the connectivity like the system of Interact Office, POE, tunable white.

Benefits

- High energy saving
- Covers most types of ceilings with different size of 200X1200, 300X1200, 600X600 and 600X1200
- Good light quality
- Reliable performance
- Easy maintenances and installation
- Office compliant UGR19 and UGR16 versions are available for better visual comfort

Features

- System efficiency 110lm/W (non UGR19/16 versions)
- CRI >80, SDCM 4
- Lifetime: 50k hours (L80@25deg)
- UGR19 and UGR16 available for certain types
- IP44 front/IP20 back available for certain types

Application

- Offices
- Residential

GreenPerform Panel

Versions



Green Perform Panel 4 60 60

Green Perform Panel 30 120

Dimensional drawing

