



Slim with high efficacy

GreenPerform Panel

GreenPerform Panel RC160 is a slim Panel with high efficacy in the market. It offers two lumen options with four dimension types, 200X1200, 300X1200, 600x600,600x1200, and three mounting options, recessed, suspended and plaster ceiling. It also offers the connectivity like the system of Interact Office, POE, tunable

Benefits

white.

- · High energy saving
- Covers most types of ceilings with different size of 200X1200, 300X1200, 600X600 and 600X1200
- · Good light quality
- · Reliable performance
- \cdot Easy maintenances and installation
- · Office compliant UGR19 and UGR16 versions are available for better visual comfort

Features

- · System efficiency 110lm/W (non UGR19/16 versions)
- CRI >80, SDCM 4
- · Lifetime: 50k hours (L80@25deg)
- · UGR19 and UGR16 available for certain types
- IP44 front/IP20 back available for certain types

Application


- Offices
- Residential


Versions





60 60+logo fa 30 120+logo fa Green Perform Panel 60 120 Green Perform Panel 30 120


Dimensional drawing















Dimensional drawing



General Information	
CE mark	CE mark
ENEC mark	-
Flammability mark	-
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Temperature	
Ambient temperature range	-20 to +45 °C
Mechanical and Housing	
Housing Color	White
Over Time Performance (IEC Co	mpliant)
Median useful life L80B50	50,000 hour(s)

General Information (1/2)

3

		Driver		Light source	Number of
Order Code	Full Product Name	included	Glow-wire test	replaceable	gear units
911401719602	RC160V LED40S 840	Yes	Temperature 650	No	1 unit
	W60L60 PSU OC CAU		°C, duration 30 s		
911401719612	RC160V LED40S 840	Yes	Temperature 650	No	1 unit
	W30L120 PSU OC CAU		°C, duration 30 s		
911401728632	RC160X LED40S TW	-	-	-	-
	W60L60 PSD				
911401728642	RC160X LED40S TW	-	-	-	-
	W60L60 PSD OC IP44				
911401755012	RC160V LED40S 840	-	-	-	-
	W60L60 PSD OC CAU				
911401755982	RC160X LED40S 840	-	-	-	-
	W60L60 OC SW				
911401738082	RC160V LED40S 840	-	-	-	-
	W60L120 PSU OC CAU				
911401755022	RC160V LED40S 840	-	-	-	-
	W30L120 PSD OC CAU				
911401755052	RC160X LED40S 840	-	-	-	-
	W30L120 IAP OC CAU				

General Information (2/2)

Order Code	Full Product Name	Service tag
911401719602	RC160V LED40S 840 W60L60 PSU OC CAU	Yes
911401719612	RC160V LED40S 840 W30L120 PSU OC CAU	Yes
911401728632	RC160X LED40S TW W60L60 PSD	-
911401728642	RC160X LED40S TW W60L60 PSD OC IP44	-
911401755012	RC160V LED40S 840 W60L60 PSD OC CAU	-

Order Code	Full Product Name	Service tag
911401755982	RC160X LED40S 840 W60L60 OC SW	-
911401738082	RC160V LED40S 840 W60L120 PSU OC CAU	-
911401755022	RC160V LED40S 840 W30L120 PSD OC CAU	-
911401755052	RC160X LED40S 840 W30L120 IAP OC CAU	-

Light Technical (1/2)

Order Code	Full Product	Beam angle of light	Correlated Color Temperature	Optical cover	Luminous Efficacy (rated)
911401719602	RC160V LED40S 840 W60L60 PSU	- degree(s)	(Nom) 4000 K	Polystyrene bowl/cover prismatic	(Nom) 110 lm/W
911401719612	OC CAU RC160V LED40S 840 W30L120 PSU OC CAU	- degree(s)	4000 K	Polystyrene bowl/cover prismatic	110 lm/W
911401728632	RC160X LED40S TW W60L60 PSD	-	3000 K	Acrylate cover and semi-matt high-reflective optic	85 lm/W
911401728642	RC160X LED40S TW W60L60 PSD OC IP44	-	3000 K	Acrylate cover and semi-matt high-reflective optic	85 lm/W
911401755012	RC160V LED40S 840	-	4000 K	Acrylate cover and semi-matt	110 lm/W

	Full Product	Beam angle of light	Correlated Color Temperature	Optical cover	Luminous Efficacy (rated)
Order Code	Name	source	(Nom)	type	(Nom)
	W60L60 PSD			high-reflective	
	OC CAU			optic	
911401755982	RC160X	-	4000 K	Acrylate cover	110 lm/W
	LED40S 840			and semi-matt	
	W60L60 OC			high-reflective	
	SW			optic	
911401738082	RC160V	-	4000 K	Acrylate cover	110 lm/W
	LED40S 840			and semi-matt	
	W60L120			high-reflective	
	PSU OC CAU			optic	
911401755022	RC160V	-	4000 K	Acrylate cover	110 lm/W
	LED40S 840			and semi-matt	
	W30L120			high-reflective	
	PSD OC CAU			optic	
911401755052	RC160X	-	4000 K	Acrylate cover	110 lm/W
	LED40S 840			and semi-matt	
	W30L120 IAP			high-reflective	
	OC CAU			optic	

Light Technical (2/2)

_			
Order Code	Full Product Name	Luminous Flux	Optic type
911401719602	RC160V LED40S 840 W60L60 PSU OC CAU	4,000 lm	Wide beam
911401719612	RC160V LED40S 840 W30L120 PSU OC	4,000 lm	Wide beam
	CAU		
911401728632	RC160X LED40S TW W60L60 PSD	3,200 lm	-
911401728642	RC160X LED40S TW W60L60 PSD OC IP44	3,200 lm	-
911401755012	RC160V LED40S 840 W60L60 PSD OC CAU	4,000 lm	_

Order Code	Full Product Name	Luminous Flux	Optic type
911401755982	RC160X LED40S 840 W60L60 OC SW	4,000 lm	-
911401738082	RC160V LED40S 840 W60L120 PSU OC	4,000 lm	-
	CAU		
911401755022	RC160V LED40S 840 W30L120 PSD OC	4,000 lm	-
	CAU		
911401755052	RC160X LED40S 840 W30L120 IAP OC CAU	4,000 lm	-

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
911401719602	RC160V LED40S 840 W60L60	50 to 60 Hz	36 W
	PSU OC CAU		
911401719612	RC160V LED40S 840 W30L120	50 to 60 Hz	36 W
	PSU OC CAU		
911401728632	RC160X LED40S TW W60L60	50 or 60 Hz	38 W
	PSD		
911401728642	RC160X LED40S TW W60L60	50 or 60 Hz	38 W
	PSD OC IP44		
911401755012	RC160V LED40S 840 W60L60	50 or 60 Hz	36 W
	PSD OC CAU		

Order Code	Full Product Name	Line Frequency	Power Consumption
911401755982	RC160X LED40S 840 W60L60	50 or 60 Hz	36 W
	OC SW		
911401738082	RC160V LED40S 840 W60L120	50 or 60 Hz	36 W
	PSU OC CAU		
911401755022	RC160V LED40S 840 W30L120	50 or 60 Hz	36 W
	PSD OC CAU		
911401755052	RC160X LED40S 840 W30L120	50 or 60 Hz	36 W
	IAP OC CAU		

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401719602	RC160V LED40S 840 W60L60 PSU OC CAU	No
911401719612	RC160V LED40S 840 W30L120 PSU OC CAU	No

Order Code	Full Product Name	Dimmable
911401728632	RC160X LED40S TW W60L60 PSD	Yes
911401728642	RC160X LED40S TW W60L60 PSD OC IP44	Yes

4

Order Code	Full Product Name	Dimmable
911401755012	RC160V LED40S 840 W60L60 PSD OC CAU	Yes
911401755982	RC160X LED40S 840 W60L60 OC SW	Yes
911401738082	RC160V LED40S 840 W60L120 PSU OC CAU	No

Order Code	Full Product Name	Dimmable
911401755022	RC160V LED40S 840 W30L120 PSD OC CAU	Yes
911401755052	RC160X LED40S 840 W30L120 IAP OC CAU	Yes

Approval and Application

			Mech.	Ingress
		Protection class	protection	protection
Order Code	Full Product Name	IEC	code	code
911401719602	RC160V LED40S 840	Safety class II	IK03	IP20
	W60L60 PSU OC CAU			
911401719612	RC160V LED40S 840	Safety class II	IK03	IP20
	W30L120 PSU OC CAU			
911401728632	RC160X LED40S TW	Safety class III	-	IP20
	W60L60 PSD			
911401728642	RC160X LED40S TW	Safety class III	-	IP20/44
	W60L60 PSD OC IP44			
911401755012	RC160V LED40S 840	Safety class III	-	IP20
	W60L60 PSD OC CAU			

			Mech.	
			impact	Ingress
		Protection class	protection	protection
Order Code	Full Product Name	IEC	code	code
911401755982	RC160X LED40S 840	Safety class III	-	IP20
	W60L60 OC SW			
911401738082	RC160V LED40S 840	Safety class III	-	IP20
	W60L120 PSU OC CAU			
911401755022	RC160V LED40S 840	Safety class III	-	IP20
	W30L120 PSD OC CAU			
911401755052	RC160X LED40S 840	Safety class III	-	IP20
	W30L120 IAP OC CAU			

Initial Performance (IEC Compliant)

		Initial	Luminous flux
Order Code	Full Product Name	chromaticity	tolerance
911401719602	RC160V LED40S 840 W60L60 PSU	(0.43, 0.40)	+/-5%
	OC CAU	SDCM<4	
911401719612	RC160V LED40S 840 W30L120 PSU	(0.43, 0.40)	+/-5%
	OC CAU	SDCM<4	
911401728632	RC160X LED40S TW W60L60 PSD	-	+/-10%
911401728642	RC160X LED40S TW W60L60 PSD	-	+/-10%
	OC IP44		
911401755012	RC160V LED40S 840 W60L60 PSD	-	+/-10%
	OC CAU		

		Initial	Luminous flux
Order Code	Full Product Name	chromaticity	tolerance
911401755982	RC160X LED40S 840 W60L60 OC	-	+/-10%
	SW		
911401738082	RC160V LED40S 840 W60L120 PSU	-	+/-10%
	OC CAU		
911401755022	RC160V LED40S 840 W30L120 PSD	-	+/-10%
	OC CAU		
911401755052	RC160X LED40S 840 W30L120 IAP	-	+/-10%
	OC CAU		

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401719602	RC160V LED40S 840 W60L60 PSU OC CAU	Not applicable
911401719612	RC160V LED40S 840 W30L120 PSU OC CAU	Not applicable
911401728632	RC160X LED40S TW W60L60 PSD	-
911401728642	RC160X LED40S TW W60L60 PSD OC IP44	-
911401755012	RC160V LED40S 840 W60L60 PSD OC CAU	-

Order Code	Full Product Name	Maximum dim level
911401755982	RC160X LED40S 840 W60L60 OC SW	-
911401738082	RC160V LED40S 840 W60L120 PSU OC CAU	-
911401755022	RC160V LED40S 840 W30L120 PSD OC CAU	-
911401755052	RC160X LED40S 840 W30L120 IAP OC CAU	-



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.