



High Power Floodlight with True Modularity.

UniFlood M

UniFlood M is a modular, rectangular shaped, cost effective and exterior-rated architectural LED floodlight that is designed for façade, landscape and outdoor flood lighting applications. The robust mechanical design and high-efficient optical design make it ideal for illuminating multi-story exterior facades, bridges, landmarks and monuments. Available in white, monochromatic colours, RGB, RGBW and tunable white. Eight different spread lenses ranging from narrow spot, to wide flood and DMX512/RDM control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Each head can be tilted separately.
- Each head can be controlled separately (optional)
- Eight different spread lenses ranging from narrow spot to wide flood
- DMX512/RDM control option
- 1-foot-candle at up to 200 m
- Robust Design and IP66 rating for outdoor use

Features

- Standard: RGBW, RGB, 2,700 K, 3,000 K and 4,000 K
- Optional 5,000 K, Monochromatic Colours and Tunable White
- Flexible lengths from 300 to 750 mm
- Adjustable tilting angles for each head and for the whole set
- Steel brackets

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and squares

UniFlood M

Warnings and Safety

- For outdoor use only.

