



Tango G4 LED lighting brightens your world

Tango G4 LED Flood

Philips Tango G4 LED flood lighting is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

Benefits

- Energy-saving
- Applicable for many more lighting applications
- Weight is upto 23% down and windage area is upto 35% less than Tango G3 LED.
- Brighter and safe
- Robust and reliable

Features

- Higher system efficacy - typically 140 lm/W
- Full-range of lumen packages for all applications
- Multiple optics to accommodate all customer needs
- High-quality ADC1 die-cast aluminium housing and steel bracket
- 500 hrs (small and medium housing) and 1,000 hrs (large housing) salt spray pass for option, IP66 and IK08 protection.

Tango G4 LED Flood

Application

- General flood lighting
- Large industrial areas / Car Park Areas
- Billboard
- Airport Apron
- Port & Container Yard
- Building facades
- Transportation Terminals & Tollways
- Recreational Sports Stadium

Warnings and Safety




- please pay attention to the mounting instructions

Specifications

Material	Housing: die-cast aluminum
	Optics: polycarbonate
Light Source	3030 and SQ5 LED module
Installation	U bracket surface-mounted
Luminous flux	BVP431/BVP491: ~13,000lumen
	BVP432/BVP492: ~27,000lumen
	BVP433/BVP493: ~52,000lumen
Correlated color temperature - CCT	3000K / 4000K/ 5700K
Luminaire efficacy	Up to 140lm/W

Color Rendering index - 70/80	
CRI	
Power	Up to 380W
Mains Voltage	220-240V, 50/60Hz
Control system input	DALI / 1-10V / coded mains
Dimming	DALI / 1-10V / coded mains
Operating Temperature range	-40 to +50 °C (outdoor)
Ingress protection	IP66
Certification	IECEE CB, CQC, CE, SAA

Dimensional drawing



Tango G4 LED Flood

General Information	
CE mark	CE mark
Driver included	Yes
Light Technical	
Light source color	740 neutral white
Correlated Color Temperature (Nom)	4000 K
Optical cover type	Polycarbonate bowl/cover
Color rendering index (CRI)	>70
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP66

Light Technical

Order Code	Full Product Name	Luminous Flux
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	6,800 lm
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	6,700 lm
911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	9,200 lm
911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	9,200 lm
911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	9,100 lm
911401681806	BVP431 LED92/NW 70W SWB ANZ CL	9,200 lm
911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	13,600 lm
911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	13,400 lm
911401683706	BVP431 LED136/NW 100W SWB ANZ CL	13,600 lm
911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	20,600 lm
911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	20,300 lm
911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	27,400 lm
911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	27,400 lm
911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	27,100 lm
911401691406	BVP432 LED274/NW 200W SWB ANZ CL	27,400 lm
911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	41,300 lm
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	41,300 lm
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	40,900 lm
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	38,200 lm
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	41,800 lm
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	46,500 lm
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	46,500 lm
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	46,000 lm
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	43,000 lm
911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	51,700 lm
911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	51,100 lm
911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	47,700 lm
911401606907	BVP433 LED522/NW 220~240V 380W NB GM	52,200 lm
911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	52,200 lm
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	31,000 lm
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	31,000 lm
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	30,700 lm
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	28,600 lm
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	31,300 lm
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	34,400 lm
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	34,400 lm
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	34,100 lm
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	34,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	50 W	911401683706	BVP431 LED136/NW 100W SWB ANZ CL	100 W
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	50 W	911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	120 W
911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	70 W	911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	150 W
911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	70 W	911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	200 W
911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	70 W	911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	200 W
911401681806	BVP431 LED92/NW 70W SWB ANZ CL	70 W	911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	200 W
911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	100 W	911401691406	BVP432 LED274/NW 200W SWB ANZ CL	200 W
911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	100 W	911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	305 W

Tango G4 LED Flood

Order Code	Full Product Name	Power Consumption
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	305 W
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	305 W
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	305 W
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	305 W
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	345 W
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	345 W
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	345 W
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	345 W
911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	380 W
911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	380 W
911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	380 W

Order Code	Full Product Name	Power Consumption
911401606907	BVP433 LED522/NW 220~240V 380W NB GM	380 W
911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	380 W
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	230 W
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	230 W
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	230 W
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	230 W
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	230 W
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	255 W
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	255 W
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	255 W
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	255 W

