

# Day-Brite

## CFI

by @signify

Industrial

HCX

Sealed high bay



## Modern industrial design, energy-saving technology

Functional high bay lighting has a new look with Day-Brite / CFI HCX LED sealed high bay luminaires.

You don't need to sacrifice smart looks for affordable, dependable lighting in your functional spaces anymore. This Sealed high bay delivers up to 22,000 lumens

with efficacies up to 129 LPW. Bring your retail and institutional spaces to life with this cost-effective luminaire built to last with a corrosion-resistant finish.

No more sacrifice, just great looks, dependability and energy-savings.



# HCX LED sealed high bay

Indoor



## Performance meets style

- Die cast frame and driver containment housing.
- Heavy duty eyelet provided for connection to customer-supplied suspension.
- Lumen maintenance up to 70% (L70) at 50,000 hours.
- Exposed leads for wiring connection with sleeving for environmental protection.
- cULus listed for use in wet locations up to 40C ambient.
- IP65 rated
- Components are RoHS compliant.


## Ordering guide

Example: HCX15L840-UNV-DIM

Series	Lumens <sup>1</sup> (nominal)	Color Temp. (K)	Voltage	Dimming
<b>HCX</b>		<b>840</b> –	–	<b>DIM</b>
<b>HCX</b> Sealed high bay	<b>15L</b> 15,000 nominal delivered lumens <b>22L</b> 22,000 nominal delivered lumens	<b>840</b> 80 CRI, 4000K	<b>UNV</b> Universal voltage 120-277V <b>347</b> 347V	<b>DIM</b> 0-10V

1. Nominal delivered lumens at 25°C ambient.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

