

Wall Mount

Cylinders

300 Line Forward Throw

The Gardco 300 Line is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The Enclosed Downlight style uses high intensity discharge, incandescent or fluorescent lamps. Housings are diecast aluminum with twin architectural reveals located near the luminaire apertures. A choice of two (2) light control styles and four (4) mounting options is available. Luminaires are finished with a fade and abrasion resistant polyester powder coat offered in six (6) standard colors. 300 Line Enclosed Downlight luminaires provide full cutoff performance.

	-

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Ordering Guide

Model Mounting Voltage Options 300 300 U Enclosed A¹ Arm Mount FT/C Lens. Clear dual **T70MH** 120 BRP Bronze Paint F Fusing Uplight to Pole assembly with 277 BLP Black Paint PCB Button Type (2" x 5" arm) Forward Throw WP White Paint Photocontrol C Ceiling D Enclosed Reflector NP Natural (W mount only Downlight \mathbf{P}^2 Pendant Aluminum ws Wall Mounted w Wall FT/C Lens. Clear flat Paint J-Box for with Forward BGP Beige Paint Surface Conduit Throw Reflector Verde Green (W mount only) VP Paint Luminaires cannot be field ос Optional modified to change optics Color Paint or lamp types. Specify RAL designation ex: OC-RAL7024 SC Special Color Paint Specify. Must supply color chip

Enter the order code into the appropriate box above. Note: Gardco reserves the right to refuse a configuration. Not all combinations and configurations are valid. Refer to notes below for exclusions and limitations. For questions or concerns, please consult the factory.

1. Indicate Arm Length, ex. "A6" is for a 6" arm length. Available in 6" incremental lengths from 6" minimum up to 48" maximum. Maximum arm length is 48". Standard length is 6", and will be provided if no length is indicated. If not mounted to top of pole, an additional handhole on pole is required to permit installation. Provide information as to size and type of pole.

2. Indicate Pendant Length, ex. "P18" is for a 18" pendant length. Stated length is the distance from the ceiling to the top of the luminaire and takes into account the mounting hardware. Available in 6" incremental lengths from 6" minimum up to 144" maximum. Maximum pendant length is 144". Standard length is 18", and will be provided if no length is indicated.

example: 300DA6L70MH120BRPF

Lamp/Voltage Chart

Voltage:	120	208	240	277	347	480				
T6 / G12										
ттомн										
MH - Metal Halide (Pulse Start) HPS - High Pressure Sodium QF - Quad Fluorescent TRF - Triple Tube Fluorescent										
Luminaires cannot be field modified to change optics or lamp types.										

Specifications

HOUSING

Housings are die cast aluminum in a single-piece cylindrical form of corrosion resistant alloy, 1/8" min. wall thickness. Units are 7.5" in diameter and 12" in height, nominal measurements.

MOUNTING

Arm Mount to Pole (A): Luminaire mounts to pole with an extruded aluminum 2" x 5" arm. Available in 6" incremental lengths from 6" minimum up to 48" maximum. Maximum arm length is 48". Standard length is 6", and will be provided if no length is indicated. If not mounted to top of pole, an additional handhole on pole is required to permit installation. Provide information as to size and type of pole. Ceiling (C): Provides for direct ceiling mount as shown.

Pendant Assembly (P): Swivel pendant assembly with locking set screws. Stated length is the distance from the ceiling to the top of the luminaire and takes into account the mounting hardware. Available in 6" incremental lengths from 6" minimum up to 144" maximum. Maximum pendant length is 144". Standard length is 18", and will be provided if no length is indicated. Swivel pendant can accommodate 35° sloped ceiling maximum.

Wall Bracket (W): Cast aluminum canopy with integrated aluminum arm secured to housing with (2) 5/16" bolts. Requires mounting to a structural member of the building.

LIGHT CONTROL (TRIM)

Lens (L): Lens units consist of a Solite® glass lens mounted

to a die cast aluminum trim support assembly. Lens with Louver (LL): Lens with louver units consist of a Solite® glass lens mounted to a die cast aluminum trim support assembly, including 1 5/8" x 1 5/8" square louvers with a nominal depth of 1".

ELECTRICAL

Internal ballast will be provided based on the specified lamp configuration. Standard fluorescent ballasts are solid state. Fluorescent units have a starting temperature of O°F (-18°C).

LAMPHOLDER

Pulse rated medium base lampholders are glazed porcelain with nickel-plated screw shell. Fluorescent lampholders are high temperature thermoplastic (PBT) with brass alloy contacts.

FINISH

Each luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, textured TGIC polyester powder coat finish.

LABELS

All luminaires bear UL or CUL (where applicable) Wet Location labels.


WARRANTY

Gardco luminaires feature a 5 year limited warranty. See Warranty Information on www. sitelighting.com for complete details and exclusions. Polycarbonate lenses carry a 1 year warranty only.

FULL CUTOFF PERFORMANCE: Full cutoff performance means a luminaire distribution where zero candela intensity occurs at an angle of 90° above nadir. Additionally, the candela per 1000 lamp lumens does not numerically exceed 100 (10 percent) at a vertical angle of 80° above nadir. This applies to all lateral angles around the luminaire.

CUTOFF PERFORMANCE: Cutoff performance means a luminaire distribution where the candela per 1000 lamp lumens does not numerically exceed 25 (2.5 percent) at an angle at or above 90° above nadir, and 100 (10 percent) at a vertical angle of 80° above nadir. This applies to all lateral angles around the luminaire.

Dimensions



Signify

© 2019 Signify Holding B.V. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication signify com/outdoorluminaires

10-300_LINE_FT_Spec_Sheet 12/18 page 3 of 3

Signify, North America Corp., 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216 Signify, Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008