



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide

Example: BL616 A S7 BAB

Product Code	Finish	Mounting	Lamp
BL616		S7	BAB
BL616 Aluminum Bullyte	A Black H Bronze	S7 Mounting Stake	BAB 20W MR16

- Each product will ship with an S7
- BAB Lamp is optional

Specifications

Housing

½" NPS male threads to screw onto accessory mounting stake or junction box. Die-cast marine grade aluminum alloy. Fully rotatable shroud, gasketed, die-cast marine grade aluminum alloy. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

Optical Assembly

Clear tempered glass lens.

Lamping

50W maximum MR16 bi-pin lamp. Lower wattage lamps are acceptable.

Electrical Assembly

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

Warranty

Three-year limited warranty.

Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width

3" (77mm)

Length

5 ½" (141mm)

Max. Weight

1.04 lb.

