

# POWER CABLE



**SAMPLE CATALOG NUMBER: PC-12-1E-10**

<b>PC</b>	<b>12</b>	
<u>DESIGNATOR</u> PC – Power Cable	<u>WIRING CONFIGURATION</u> <b>1E</b> – 1 circuit equipment ground <b>2E</b> – 2 circuit equipment ground <b>3E</b> – 3 circuit equipment ground <b>1I</b> – 1 circuit isolated ground <b>2I</b> – 2 circuit isolated ground <b>NE</b> – 2 circuit/2 neutral	
	<u>VOLTAGE</u> <b>12</b> – 120v	<u>LENGTH</u> <b>10</b> – 10' <b>15</b> – 15' <b>20</b> – 20'

### APPLICATION

- Pre-fabrication cables replace conventional conduit and wire to distribute receptacle power circuits.

### ELECTRICAL

- UL/cUL listed.

### CONSTRUCTION

- Pre-wired with male (power-in), female (power-out) configuration.
- Internal wires are #12 AWG THHN stranded copper, 600 volt, plus a bare #12 AWG solid tinned copper ground conductor. An isolated ground conductor of #12 AWG THHN stranded copper, 600 volt, is also available.
- Cable head is 18 gauge steel, zinc plated.
- Spring steel latches are on the male (power-in) cable head.
- Single circuit, two circuit and three circuit cable with equipment ground cable sets are available.
- Single circuit and two circuit with equipment ground and isolated ground cable sets are available.
- Galvanized steel cable.

**Job Name:**


Catalog Number:

Type:


Notes:

ecp5015


**DIMENSIONS**



**APPLICATION**



**WIRING**



**WIRING DIAGRAM**

