

# Halogen non-reflector

## 6390 30W G5.3 10.8V 1CT/24

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information	
Base	G5.3 [ G5.3]
Philips Code	6390
ANSI Code	DZA
LIF Code	-
Operating Position	Base Down +/- 90 D [ Base Down +/- 90 D]
Main Application	Projection
Life to 50% Failures (Nom)	1000 h

Light Technical	
Luminous Flux (Rated) (Nom)	570 lm
Correlated Color Temperature (Nom)	3100 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	30 W
Voltage (Nom)	10.8 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Filament Shape	Flat
Filament Dimensions WxH	3.5x1.25


Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C

Product Data	
Order product name	6390 30W G5.3 10.8V 1CT/24
EAN/UPC - Product	8718696690215
Order code	324004
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	822234361803
Net Weight (Piece)	7.000 g

## Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
6390 30W	8.5 mm	26.75	27.25	27	1.65 mm	1.50	1.47 mm	44 mm
G5.3 10.8V		mm	mm	mm		mm		
1CT/24								

6390 30W G5.3 10.8V

