



LED Bollard II

BCP150 LED150/NW PSU 220-240V 7043

LED Bollard II, 200 lm, 7 W, 740 neutral white, Safety class I, Baseplate

People want to create a pleasant atmosphere around their property – something that will catch visitors’ attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience with optimized-quality lighting at minimum cost. Combining reliable low-power LEDs and an integrated driver, the robustly designed LED Bollard II delivers an affordable LED lighting solution to meet your landscaping needs.

Product data

General Information	
Lamp family code	LED-LP [LED Low Power]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Embedded control	-
CE mark	CE mark
Warranty period	1 years
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	28.57 lm/W

Color rendering index (CRI)	>70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	7 W
Power Factor (Fraction)	0.4
Connection	Screw connection block
Cable	Cable without plug 3-pole
Number of products on MCB of 16 A type B 1	
Temperature	
Ambient temperature range	-20 to +40 °C

LED Bollard II

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum extruded
Optical cover material	Polycarbonate
Housing Color	Dark gray
Mounting device	Baseplate
Optical cover finish	Matte
Overall height	500 mm
Overall diameter	180 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BCP150 LED150/NW PSU 220-240V 7043
Full product name	BCP150 LED150/NW PSU 220-240V 7043
Full product code	910403307802
Local code description	BCP150L150NWDG
Order code	910403307802
Material Nr. (12NC)	910403307802
Local order code	BCP150L150NWDG
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163278896
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163279299

Dimensional drawing

