



DecoScene LED BBP621

BBP621 15xLED-HB/NW | NB GC GR RMR

DecoScene LED Accent - 15 pcs - LED High Brightness - Narrow beam - Clear glass - Recessed mounting box round

Whether floodlighting a piece of architecture or creating accent effects, for many designers the ideal luminaire would be invisible. With their recessed housings, in-ground floodlights are about as close as it gets to this ideal situation. DecoScene LED has been designed to deliver the optimal upward lighting effect – from high-powered floodlighting to more subtle effects such as accent lighting. Its unique collimating optic delivers a uniform light output and ensures optimum color mixing. Square and round housings fit snugly into paving, concrete or grass, leaving the surface flush and unobtrusive during the day. The combination of the latest LED technology and best-in-class optics makes DecoScene LED a totally flexible solution – easy to install, no matter where, and creating a perfect lighting effect.

Product data

General Information			
Number of light sources	15 [15 pcs]	Embedded control	No [-]
Lamp family code	LED-HB [LED High Brightness]	Control interface	-
Lamp version	2S [2nd generation, screw fixation]	Connection	No [-]
Light source colour	Neutral white	Cable	Cable 3.0 m without plug (C3K)
Light source replaceable	Yes	Protection class IEC	Safety class I (I)
Number of gear units	1 unit	Luminaire shape	Round version - to be replaced by RND
Driver/power unit/transformer	PSU [Power supply unit]	Coating	-
Driver included	Yes	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Optical cover/lens type	GC [Clear glass]	Flammability mark	NO [-]
Luminaire light beam spread	12°	CE mark	CE mark
		ENEC mark	ENEC mark

DecoScene LED BBP621

Green flagship mark	Green Flagship
Lifetime to 70% luminous flux	50000 h
Warranty period	3 years
Mechanical accessories	No [-]
Decorative accessories	No [-]
Outdoor optic type	Narrow beam
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB	32
LED engine type	LED
Product Family Code	BBP621 [DecoScene LED Accent]

Light Technical

Upward light output ratio	0.03
Standard tilt angle post-top	-
Standard tilt angle side entry	-

Operating and Electrical

Input voltage	100 to 277 V
Input frequency	50 to 60 Hz
Inrush current	35 A
Inrush time	0.35 ms
Power factor (min.)	0.8

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Tempered glass
Fixation material	Steel
Mounting device	RMR [Recessed mounting box round]
Optical cover/lens shape	Convex lens
Optical cover/lens finish	Clear

Overall height	430 mm
Overall diameter	200 mm
Effective projected area	0 m²
Colour	Gray
Dimensions (height x width x depth)	430 x NaN x NaN mm (16.9 x NaN x NaN in)

Approval and Application

Ingress protection code	IP67 [Dust penetration-protected, watertight]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge protection (common/differential)	Luminaire surge protection level up to 4 kV differential mode and 4 kV common mode

Initial Performance (IEC Compliant)

Initial luminous flux	1875 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	67.0 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	70
Initial chromaticity	(0.367, 0.396) SDCM <3
Initial input power	28 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable


Product Data

Full product code	871829141878800
Order product name	BBP621 15xLED-HB/NW I NB GC GR RMR
EAN/UPC – product	8718291418788
Order code	41878800
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910403947512
Net weight (piece)	7.125 kg



DecoScene LED BBP621

Dimensional drawing




DecoScene LED Accent BBP621/623

Photometric data

BBP621 GC 15xLED-HBNW NB

LGR=0.73

15 x 125 lm



OFCC1_BBP621 GC 15xLED-HBNW NB.EPS

