



DecoScene LED BBP623

BBP623 34xLED-HB/NW II MB GC GR RMR

DecoScene LED Accent, 34, LED High Brightness, Medium beam, Clear glass, Recessed mounting box round

Whether floodlighting a piece of architecture or creating accent effects, for many designers the ideal luminaire would be invisible. With their recessed housings, inground floodlights are about as close as it gets to this ideal situation. DecoScene LED has been designed to deliver the optimal upward lighting effect – from high-powered floodlighting to more subtle effects such as accent lighting. Its unique collimating optic delivers a uniform light output and ensures optimum color mixing. Square and round housings fit snugly into paving, concrete or grass, leaving the surface flush and unobtrusive during the day. The combination of the latest LED technology and best-in-class optics makes DecoScene LED a totally flexible solution – easy to install, no matter where, and creating a perfect lighting effect.

Product data

General Information	
Lamp family code	LED-HB [LED High Brightness]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)

	value also represents the B10 value. * At
	extreme ambient temperatures the luminaire
	might automatically dim down to protect
	components
Light source engine type	LED
Product family code	BBP623 [DecoScene LED Accent]
Lighting Technology	LED
Value ladder	Performance
Embedded control	-
CE mark	Yes
Warranty period	3 years

Datasheet, 2023, October 9 data subject to change


DecoScene LED BBP623

Flammability mark	
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes
- Lo Koris computant	163
Light Technical	
Upward light output ratio	0.03
Luminous Flux	4,250 lm
Standard tilt angle posttop	
Standard tilt angle side entry Correlated Color Temperature (New)	4000 K
Correlated Color Temperature (Nom)	
Luminous Efficacy (rated) (Nom)	78.7 lm/W
Color rendering index (CRI)	70
Number of light sources	Noutral white
Light source color Optical cover type	Neutral white Clear glass
Optical cover type	24°
Luminaire light beam spread	Medium beam
Optic type outdoor	Medium beam
Operating and Electrical	
	100 1- 277 /
Input Voltage	100 to 277 V
Line Frequency	50 to 60 Hz
Inrush current	35 A
Inrush time	0.35 ms
Power Consumption	0.8
Power Factor (Fraction)	0.8
Connection	Calala 2.0 na with a straight
Cable Name to the date of MCB of 15 A town	Cable 3.0 m without plug
Number of products on MCB of 16 A type B	32
Temperature	
	-40 to +50 °C
Ambient temperature range	-40 to +50 C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer Control interface	Power supply unit (On/Off)
	No No
Constant light output	INU .
Mechanical and Housing	
	Aluminum
Housing Material	Atuminum
Reflector material	Polycarbonato
Optic material	Polycarbonate Tompored glass
Optical cover material	Tempered glass

Fixation material	Steel
Housing Color	Gray
Mounting device	Recessed mounting box round
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall height	382 mm
Overall diameter	350 mm
Effective projected area	0 m²
Approval and Application	
Ingress protection code	IP67 [Dust penetration-protected, watertight]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV
	differential mode and 4 kV common mode
Sustainability rating	-
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.367, 0.396) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compli	iant)
Control gear failure rate at median useful	10 %
life 100000 h	
Lumen maintenance at median useful	L80
life* 100000 h	
Application Conditions	
Performance ambient temperature Tq	25 ℃
Maximum dim level	Not applicable
Product Data	
Order product name	BBP623 34xLED-HB/NW II MB GC GR RMR
Full product name	BBP623 34xLED-HB/NW II MB GC GR RMR
Full product code	871829141907500
Order code	41907500
Material Nr. (12NC)	910403950412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291419075
Numerator - Packs per outer box	
	1
EAN/UPC - Case	8718291419075

DecoScene LED BBP623

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.