



DecoScene LED BBP623

BBP623 34xLED-HB/TWH II WB GF GR DMX RMR

DecoScene LED Accent, 34, LED High Brightness, Wide beam, Glass frosted, Dynamic DMX, Recessed mounting box round

Whether floodlighting a piece of architecture or creating accent effects, for many designers the ideal luminaire would be invisible. With their recessed housings, inground floodlights are about as close as it gets to this ideal situation. DecoScene LED has been designed to deliver the optimal upward lighting effect — from high-powered floodlighting to more subtle effects such as accent lighting. Its unique collimating optic delivers a uniform light output. Round housing fits snugly into paving, concrete or grass, leaving the surface flush and unobtrusive during the day. The combination of the LED technology and best-in-class optics makes DecoScene LED a totally flexible solution — easy to install, no matter where, and creating a perfect lighting effect.

Product data

General Information		
Lamp family code	LED-HB [LED High Brightness]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper	
	"Evaluating performance of LED based	
	luminaires - January 2018": statistically there	
	is no relevant difference in lumen	
	maintenance between B50 and for example	
	B10. Therefore, the median useful life (B50)	

	value also represents the B10 value. * At	
	extreme ambient temperatures the luminaire	
	might automatically dim down to protect	
	components	
Light source engine type	LED	
Product family code	BBP623 [DecoScene LED Accent]	
Lighting Technology	LED	
Value ladder	Performance	
Embedded control	Dynamic DMX	
CE mark	Yes	
Warranty period	3 years	


Datasheet, 2023, December 5 data subject to change

DecoScene LED BBP623

		_	
Flammability mark	-	Housing Color	Grey
ENEC mark	ENEC mark	Mounting device	Recessed mounting box round
Glow-wire test	Temperature 650 °C, duration 5 s	Optical cover shape	Convex lens
EU RoHS compliant	Yes	Optical cover finish	Frosted
		Overall height	382 mm
Light Technical		Overall diameter	350 mm
Upward light output ratio	0.03	Effective projected area	O m²
Luminous Flux	3,910 lm		
Standard tilt angle posttop	-	Approval and Application	
Standard tilt angle side entry	-	Ingress protection code	IP67 [Dust penetration-protected, watertight
Correlated Color Temperature (Nom)	2700 6500 K	Mech. impact protection code	IK10 [20 J vandal-resistant]
Luminous Efficacy (rated) (Nom)	72.4 lm/W	Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV
Color rendering index (CRI)	80		differential mode and 4 kV common mode
Number of light sources	34	Protection class IEC	Safety class II
Light source color	Tunable white		
Optical cover type	Glass frosted	Initial Performance (IEC Compliant)
Luminaire light beam spread	38°	Luminous flux tolerance	+/-7%
Optic type outdoor	Wide beam	Initial chromaticity	(0.585, 0.595) SDCM <3
		Power consumption tolerance	+/-10%
Operating and Electrical		Init. Color Rendering Index Tolerance	+/-2
Input Voltage	100 to 277 V		
Line Frequency	50 to 60 Hz	Over Time Performance (IEC Comp	liant)
Inrush current	35 A	Control gear failure rate at median useful $$ 10 $\%$	
Inrush time	0.35 ms	life 100000 h	
Power Consumption	54 W	Lumen maintenance at median useful	L80
Power Factor (Fraction)	0.8	life* 100000 h	
Connection	-	<u> </u>	
Cable	Cable 3.0 m without plug	Application Conditions	
Number of products on MCB of 16 A type	e 32	Performance ambient temperature Tq	25 ℃
В		Maximum dim level	0% (digital)
Temperature		Product Data	
Ambient temperature range	-40 to +50 °C	Order product name	BBP623 34xLED-HB/TWH II WB GF GR DMX
			RMR
Controls and Dimming		Full product name	BBP623 34xLED-HB/TWH II WB GF GR DMX
Dimmable	Yes		RMR
Driver/power unit/transformer	Power supply unit (On/Off)	Full product code	871829141932700
Control interface	Dynamix DMX	Order code	910403952912
Constant light output	No	Material Nr. (12NC)	910403952912
		Numerator - Quantity Per Pack	1
Mechanical and Housing		EAN/UPC - Product/Case	8718291419327
Housing Material	Aluminum	Numerator - Packs per outer box	1
Reflector material	-	EAN/UPC - Case	8718291419327
Optic material	Polycarbonate		
Optical cover material	Tempered glass	_	

DecoScene LED BBP623

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.