



SGS203/403

SGS203 K SON-T150W I SP

SGS203, SON-T, 150 W, Safety class I

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

Product data


General Information		Power Consumption		150 W
Lamp family code	SON-T [SON-T]	Connection		-
Gear	CONV [Conventional]	Cable		-
Photocell	-			
Product family code	SGS203 [SGS203]	Mechanical and Housing		
Embedded control	-	Housing Color		Grey
CE mark	Yes	Mounting device		-
ENEC mark	ENEC mark	Parts color		-
Light Technical		Approval and Application		
Standard tilt angle posttop	5°	Ingress protection code		IP43 [Wire-protected, rain/spray-proof]
Standard tilt angle side entry	5°	Protection class IEC		Safety class I
Number of light sources	1			
Optical cover type	Polycarbonate bowl/cover	Product Data		
Optic type outdoor	-	Order product name		SGS203 K SON-T150W I SP
		Full product name		SGS203 K SON-T150W I SP
		Full product code		871155908113700
Operating and Electrical		Order code		08113700
Input Voltage	230 V			

SGS203/403

Material Nr. (12NC)	910500043912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559081137
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559081137
----------------	---------------

Dimensional drawing



Product
SGS203 K SON-T150W I SP

