# **PHILIPS** Lighting



# **CoreLine Waterproof**

# WT120C LED18S/840 PSU L600

Coreline Waterproof, 840 neutral white, Power supply unit (On/Off)

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

#### Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

#### **Product data**

General Information	
Lamp family code	-
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Feed-through wiring	Simple connection and removable cover
	available for feed-through wiring 1-phase
	(internal wiring is not included)
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen

	maintenance between the B50 and, for
	example, the B10. Therefore, the median
	useful life (B50) value also represents the B10
	value.
Product family code	WT120C [Coreline Waterproof]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s

### **CoreLine Waterproof**

EU RoHS compliant	Yes
Light Technical	
Luminous Flux	2,100 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	119 lm/W
Colour rendering index (CRI)	≥80
Light source colour	840 neutral white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	110°
Unified Glare Rating (CEN)	24
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	8 A
Inrush time	0.060 ms
Power Consumption	17.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type	24
В	
Temperature	
Ambient temperature range	-20 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	Steel
Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey

	661 mm
Overall length	00111111
Overall width	87 mm
Overall height	96 mm
Dimensions (height x width x depth)	96 x 87 x 661 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Complian	t)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Comp	oliant)
Control gear failure rate at median usef	ul 5 %
control gear failure falle at median user	
life 50,000 h	
-	L75
life 50,000 h	L75
life 50,000 h Lumen maintenance at median useful	L75
life 50,000 h Lumen maintenance at median useful	L75
life 50,000 h Lumen maintenance at median useful life* 50,000 h	L75 25 °C
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions	
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq	25 °C
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level	25 °C Not applicable
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level	25 °C Not applicable
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching	25 °C Not applicable
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data	25 °C Not applicable Yes
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name	25 °C Not applicable Yes WT120C LED18S/840 PSU L600
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name Full product name	25 °C Not applicable Yes WT120C LED185/840 PSU L600 WT120C LED185/840 PSU L600
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name Full product name Full EOC	25 °C Not applicable Yes WT120C LED185/840 PSU L600 WT120C LED185/840 PSU L600 871829184045900
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name Full product name Full EOC Order code	25 °C Not applicable Yes WT120C LED18S/840 PSU L600 WT120C LED18S/840 PSU L600 871829184045900 84045900
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name Full product name Full EOC Order code Material no. (12 NC)	25 °C Not applicable Yes WT120C LED18S/840 PSU L600 WT120C LED18S/840 PSU L600 871829184045900 84045900 910500453335
life 50,000 h Lumen maintenance at median useful life* 50,000 h Application Conditions Performance ambient temperature Tq Maximum dim level Suitable for random switching Product Data Order product name Full product name Full product name Full EOC Order code Material no. (12 NC) SAP numerator – quantity per pack	25 °C Not applicable Yes WT120C LED185/840 PSU L600 WT120C LED185/840 PSU L600 871829184045900 84045900 910500453335 1

Textured

Optical cover/lens finish

## **CoreLine Waterproof**

#### Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, December 5 - data subject to change