



# **LuxSpace Accent Mini**

### **RS730B LED12S/930 PSE-E MB WH**

LuxSpace Accent Mini G3, LED module, system flux 1200 lm, 930 warm white, Power supply unit DC compatible, external, Medium beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications

#### **Product data**

General Information	
Lamp family code	LED12S [LED module, system flux 1200 lm]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value.
Service tag	Yes
Product family code	RS730B [LuxSpace Accent Mini G3]

Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable
	surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	133 lm/W

Datasheet, 2023, November 12 data subject to change


## **LuxSpace Accent Mini**


Color rendering index (CRI)	≥90
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Medium beam
Optical cover type	-
Luminaire light beam spread	24°
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	4.4 A
Inrush time	20 ms
Power Consumption	12.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull
	relief
Cable	-
Number of products on MCB of 16 A type	30
В	
T	
Temperature	
Ambient temperature range	+10 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-
Fixation material	-

	And in
Housing Color	White
Optical cover finish	Clear
Overall height	93 mm
Overall diameter	94 mm
Approval and Application	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IKO2 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.434, 0.403) SDCM <2
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compl	iant)
Control gear failure rate at median useful	5 %
life 50000 h	
Lumen maintenance at median useful	L80
life* 50000 h	
Application Conditions	
Performance ambient temperature Tq	25 ℃
Suitable for random switching	Yes
Product Data	
Order product name	RS730B LED12S/930 PSE-E MB WH
Full product name	RS730B LED12S/930 PSE-E MB WH
Full product code	871869684765700
Order code	910500457289
Material Nr. (12NC)	910500457289
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696847657
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696847657
· · · ·	

#### **LuxSpace Accent Mini**

#### Dimensional drawing







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.