



LuxSpace Accent Mini

RS731B LED12S/840 PSED-VLC-E WB WH

LuxSpace Accent Mini G3, LED module, system flux 1200 lm, 840 neutral white, Power supply unit with DALI interface, DC compatible for central emergency lighting, visual light communication (VLC) ready, external, Wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications, including CrispWhite for fashion stores and Food recipes for supermarkets.

Product data

General Information			
Lamp family code	LED12S [LED module, system flux 1200 lm]	Service tag	Yes
Light source replaceable	No	Product family code	RS731B [LuxSpace Accent Mini G3]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Value ladder	Specification
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

LuxSpace Accent Mini

Light Technical	
Luminous Flux	1,250 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	36°
Unified glare rating CEN	Not applicable

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	5.3 A
Inrush time	0.7 ms
Power Consumption	12 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	+10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible for central emergency lighting, visual light communication (VLC) ready, external
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated

Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall height	86 mm
Overall diameter	105 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	RS731B LED12S/840 PSED-VLC-E WB WH
Full product name	RS731B LED12S/840 PSED-VLC-E WB WH
Full product code	871869684770100
Order code	910500457294
Material Nr. (12NC)	910500457294
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696847701
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696847701

LuxSpace Accent Mini

Dimensional drawing

