



# **LuxSpace Accent Mini**

### RS741B LED20S/930 PSU-E NB WH

LuxSpace Accent Compact G3, LED Module, system flux 2000 lm, 930 warm white, Power supply unit external (On/Off), Narrow beam. White RAL 9003

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications

#### **Product data**

| General Information      |  |
|--------------------------|--|
| Lamp family code         | LED20S [LED Module, system flux 2000 lm]     |
| Light source replaceable | No   |
| Number of gear units     | 1 unit                                       |
| Driver included          | Yes  |
| Remarks                  | *-Per Lighting Europe guidance paper         |
|                          | "Evaluating performance of LED based         |
|                          | luminaires - January 2018": statistically    |
|                          | there is no relevant difference in lumen     |
|                          | maintenance between B50 and for example      |
|                          | B10. Therefore, the median useful life (B50) |
|                          | value also represents the B10 value.         |
| Service tag              | Yes  |
| Product family code      | RS741B [LuxSpace Accent Compact G3]          |
|                          |  |

| Lighting Technology                | LED                                |
|------------------------------------|------------------------------------|
| Value ladder                       | Specification                      |
| CE mark                            | Yes                                |
| Warranty period                    | 5 years                            |
| Flammability mark                  | For mounting on normally flammable |
|                                    | surfaces                           |
| ENEC mark                          | ENEC mark                          |
| Glow-wire test                     | Temperature 650 °C, duration 5 s   |
| EU RoHS compliant                  | Yes                                |
|                                    |                                    |
| Light Technical                    |                                    |
| Luminous Flux                      | 2,000 lm                           |
| Correlated Color Temperature (Nom) | 3000 K                             |
| Luminous Efficacy (rated) (Nom)    | 97 lm/W                            |
|                                    |                                    |

Datasheet, 2023, October 9 data subject to change

## **LuxSpace Accent Mini**

| Color rendering index (CRI)            | ≥90                                 |
|--|-------------------------------------|
| Number of light sources                | 1                                   |
| Beam angle of light source             | 120 degree(s)                       |
| Light source color                     | 930 warm white                      |
| Optic type                             | Narrow beam                         |
| Optical cover type                     | Clear glass                         |
| Luminaire light beam spread            | 10°                                 |
| Unified glare rating CEN               | Not applicable                      |
|  |                                     |
| Operating and Electrical               |                                     |
| Input Voltage                          | 220 to 240 V                        |
| Line Frequency                         | 50 to 60 Hz                         |
| Initial CLO power consumption          | - W                                 |
| Average CLO power consumption          | - W                                 |
| Inrush current                         | 9.92 A                              |
| Inrush time                            | 230 ms                              |
| Power Consumption                      | 20.5 W                              |
| Power Factor (Fraction)                | 0.9                                 |
| Connection                             | Push-in connector and pull relief   |
| Cable                                  | -                                   |
| Number of products on MCB of 16 A type | 65                                  |
| В                                      |                                     |
|  |                                     |
| Temperature                            |                                     |
| Ambient temperature range              | 0 to +35 ℃                          |
|  |                                     |
| Controls and Dimming                   |                                     |
| Dimmable                               | No                                  |
| Driver/power unit/transformer          | Power supply unit external (On/Off) |
| Control interface                      | -                                   |
| Constant light output                  | No                                  |
|  |                                     |
| Mechanical and Housing                 |                                     |
| Housing Material                       | Aluminum                            |
| Reflector material                     | Polycarbonate aluminum coated       |
| Optic material                         | Polycarbonate                       |
| Optical cover material                 | Polycarbonate                       |
| Fixation material                      | -                                   |
| Housing Color                          | White RAL 9003                      |
|  |                                     |

| Optical cover finish  | Clear  |
|---|--|
| Overall height  | 126 mm   |
| Overall diameter  | 130 mm   |
|   |  |
| Approval and Application  |  |
| Ingress protection code   | IP20 [Finger-protected]  |
| Mech. impact protection code  | IK02 [0.2 J standard]  |
| Protection class IEC  | Safety class II  |
|   |  |
| Initial Performance (IEC Compliant)   |  |
| Luminous flux tolerance   | +/-10%   |
| Initial chromaticity  | (0.422, 0.386) SDCM <2   |
| Power consumption tolerance   | +/-10%   |
|   |  |
| Over Time Performance (IEC Complia  | ant)   |
| Control gear failure rate at median useful  | 5 %  |
| life 50000 h  |  |
| Control gear failure rate at median useful  | 5 %  |
| life 100000 h   |  |
| Lumen maintenance at median useful life $\!\!\!^*$  | L80  |
| 50000 h   |  |
|   |  |
| Application Conditions  |  |
| Performance ambient temperature Tq  | 25 °C  |
| Maximum dim level   | Not applicable   |
|   |  |
| Suitable for random switching   | Yes  |
| Suitable for random switching   |  |
| Product Data  |  |
| <u>-</u>  |  |
| Product Data  | Yes  |
| Product Data Order product name   | Yes  RS741B LED20S/930 PSU-E NB WH   |
| Product Data Order product name Full product name   | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  |
| Product Data Order product name Full product code   | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  871869685137100   |
| Product Data Order product name Full product name Full product code Order code  | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  871869685137100  910500457642                                 |
| Product Data Order product name Full product name Full product code Order code Material Nr. (12NC)  | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  871869685137100  910500457642  910500457642                   |
| Product Data Order product name Full product name Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack                        | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  871869685137100  910500457642  910500457642  1                |
| Product Data Order product name Full product name Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack EAN/UPC - Product/Case | Yes  RS741B LED20S/930 PSU-E NB WH  RS741B LED20S/930 PSU-E NB WH  871869685137100  910500457642  910500457642  1  8718696851371 |

#### **LuxSpace Accent Mini**

#### Dimensional drawing









