



LuxSpace Accent Mini

RS751B LED49S/840 PSE-E VWB WH

LuxSpace Accent Mini, 40 W, 5150 lm, 4000 K, Very wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications

Product data

General Information			
Lamp family code	LED49S [LED module, system flux 4900 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Service tag	Yes	EU RoHS compliant	Yes
Product family code	RS751B [LuxSpace Accent Performance G3]	Light Technical	
Lighting Technology	LED	Luminous Flux	5,150 lm
Value ladder	Specification	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	129 lm/W
		Color rendering index (CRI)	≥80
		Number of light sources	1
		Beam angle of light source	120 degree(s)

LuxSpace Accent Mini

Light source color	840 neutral white
Optic type	Very wide beam
Optical cover type	-
Luminaire light beam spread	54°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	23.5 A
Inrush time	0.272 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Clear

Overall height	150 mm
Overall diameter	168 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	RS751B LED49S/840 PSE-E VWB WH
Full product name	RS751B LED49S/840 PSE-E VWB WH
Full product code	871869916724000
Order code	910500459435
Material Nr. (12NC)	910500459435
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699167240
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699167240

Dimensional drawing



LuxSpace Accent Mini

