



# GreenSpace

## DN470B LED30S/840 PSU-E C WH

GreenSpace, 28.2 W, 3300 lm, 4000 K

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information			
Lamp family code	LED30S [LED module, system flux 3000 lm]	Service tag	Yes
Cap-Base	- [-]	Product family code	DN470B [200mm]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
Light Technical			
		Luminous Flux	3,300 lm

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	117.02 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	88°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.5 A
Inrush time	0.22 ms
Power Consumption	28.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	-

Overall height	95 mm
Overall diameter	216 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* L90	50000 h
Lumen maintenance at median useful life* L80	100000 h

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	DN470B LED30S/840 PSU-E C WH
Full product name	DN470B LED30S/840 PSU-E C WH
Full product code	871869916778300
Order code	910500459483
Material Nr. (12NC)	910500459483
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699167783
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699167783

Dimensional drawing



