



SlimBlend Square, recessed

RC400B LED36S/830 PSD W60L60 VPC PIP

SlimBlend recessed mod. 600 - 830 warm white - Power supply unit with DALI interface - Push-in connector and pull relief - Safety class II (II)

Office regulation-compliant lighting with good quality of light is in demand. Moreover, there is also an increasing need for comfort-enhancing effects such as diffused lighting and lighting that smoothly blends into the ceiling architecture. That's why 'surface of light' solutions are becoming more and more popular. But parallel to these needs, are the demands to reduce energy and maintenance costs. SlimBlend answers all these needs and more. Not only does it provide glare-free comfort with a diffuse effect and clutter-free aesthetics, thanks to integrated control options, it also creates a special blending of light. It uses the 'trapped' light under the masking to create a subtle glow, with a soft transition to the edge, lowering the brightness perception and blending the light into the ceiling. SlimBlend can also be part of a connected lighting system and integrated into the IT infrastructure, enabling data on usage to be collected to help reduce energy costs and enhance employee comfort further. Also, thanks to the slim design, it enables technical equipment to be more easily installed in the plenum. Moreover, thanks to the variety of ways of mounting, various ceiling-mounted lights can take advantage of this luminaire family. SlimBlend comes in square and rectangular and can be either recessed, surface-mounted or suspended. It offers a good balance between initial cost and ROI, making it the ideal choice for delivering excellent quality of light and a fast ROI for offices.

Product data

SlimBlend Square, recessed

General Information	
Beam angle of light source	120 °
Lamp colour code	830 warm white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	No [-]
Luminaire light beam spread	120°
Control interface	DALI
Connection	PIP [Push-in connector and pull relief]
Cable	-
Protection class IEC	Safety class II (II)
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	24
RoHS mark	RoHS mark
Product Family Code	RC400B [SlimBlend recessed mod. 600]
Unified glare rating CEN	19

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Stainless steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate

Fixation material	-
Optical cover/lens finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	52 mm
Colour	White
Dimensions (height x width x depth)	52 x 597 x 597 mm (2 x 23.5 x 23.5 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	3600 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Lamp colour temperature	3000 K
Colour Rendering Index	80
Initial chromaticity	(0.43, 0.40) SDCM<3
Initial input power	36 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	Yes


Product Data

Full product code	871869917457600
Order product name	RC400B LED36S/830 PSD W60L60 VPC PIP
EAN/UPC – product	8718699174576
Order code	910500459901
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500459901
Net weight (piece)	5.600 kg



SlimBlend Square, recessed

Dimensional drawing



SlimBlend Recessed RC400B/RC402B

