



# GentleSpace Gen3

## BY481P LED350S/840 PSD NB GC SI

New Highbay - 840 neutral white - Power supply unit with DALI interface - Narrow beam - Silver RAL 9006

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

### Product data

General Information			
Beam angle of light source	114 °	Control interface	DALI
Light source colour	840 neutral white	Connection	CE [ External connector]
Light source replaceable	Yes	Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of gear units	1 unit	Protection class IEC	Safety class I (I)
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Glow-wire test	850/5 [ Temperature 850 °C, duration 5 s]
Driver included	Yes	Flammability mark	D [ For mounting on easily flammable surfaces]
Optic type	NB [ Narrow beam]	CE mark	CE mark
Luminaire light beam spread	25° x 30°	ENEC mark	ENEC mark

# GentleSpace Gen3

Warranty period	5 years
Constant light output	No
Number of products on MCB	8
Product Family Code	BY481P [ New Highbay]
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	15.3 A
Inrush time	0.061 ms
Power factor (min.)	0.9

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	600 mm
Overall width	490 mm
Overall height	85 mm
Colour	Silver RAL 9006
Dimensions (height x width x depth)	85 x 490 x 600 mm (3.3 x 19.3 x 23.6 in)

## Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]

## Initial Performance (IEC Compliant)

Initial luminous flux	35000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	148 lm/W

Init. Corr. colour temperature	4000 K
Init. colour rendering index	>80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	230 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Median useful life L70B50	100000 h
Median useful life L80B50	100000 h
Median useful life L90B50	50000 h
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

## Application Conditions

Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	45 °C
Maximum dimming level	10%
Suitable for random switching	No

## Product Data

Full product code	871869940768100
Order product name	BY481P LED350S/840 PSD NB GC SI
EAN/UPC – product	8718699407681
Order code	40768100
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500465574
Net weight (piece)	12.000 kg





# GentleSpace Gen3

## Dimensional drawing



GentleSpace gen3 BY480P-BY483P

## Photometric data



IFPC1\_BY481PPSD1xLED350S840NB

IFGU1\_BY481PPSD1xLED350S840NB

