



# **GentleSpace Gen3**

### BY481P LED250S/840 PSD MB GC WH BR

GentleSpace Gen3, 156 W, BR, 25000 lm, 4000 K, DALI, Medium beam, IP65, IK07

GentleSpace gen3 provides a smart combination of versatile offer with high efficiency, connectivity options and reliability. It provides a wide variety of options in terms of optics, beam angles (from very narrow to wide) and lumen packages, each delivering on best-in-class quality of light for enhanced safety, productivity, and comfort. With GentleSpace gen3 you can easily create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It supports changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. Additionally, a choice of mounting possibilities and pre-mounted IP65 connector enables quick and easy installation. You can choose various cover materials, special variants for extreme temperatures (XT), or hazardous areas (ATEX 2/22), or sports applications. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based system and software applications such as Interact Industry. Created with Circularity principles in mind, GentleSpace is serviceable luminaire with all information available at hand, via Signify ServiceTag app. Whether you are looking for a reliable "fit & forget" solution or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

#### **Product data**

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Product family code	BY481P [Gentlespace gen3 Large]

Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark

Datasheet, 2023, May 16 data subject to change

## **GentleSpace Gen3**

Glow-wire test	Temperature 650 °C, duration 30 s	Overall length	600 mm
EU RoHS compliant	Yes	Overall width	490 mm
Mounting	Bracket	Overall height	110 mm
		Dimensions (Height x Width x Depth)	110 x 490 x 600 mm
Light Technical			
Luminous Flux	25,000 lm	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Ingress protection code	IP65 [Dust penetration-protected, jet-
Luminous Efficacy (rated) (Nom)	160 lm/W		proof]
Color rendering index (CRI)	>80	Mech. impact protection code	IK07 [2 J reinforced]
Flickering value (PstLM) - Flickering value as	0.12	Sustainability rating	Lighting for circularity
per EN 61000-3-3		Protection class IEC	Safety class I
Stroboscopic effect visibility measure (SVM)	0.07	Photobiological risk	Photobiological risk group 1 @200mm
Beam angle of light source	114 degree(s)		EN62778
Light source color	840 neutral white		
Optic type	Medium beam	Initial Performance (IEC Compliant)	
Luminaire light beam spread	40° x 40°	Luminous flux tolerance	+/-10%
Unified glare rating CEN	Not applicable	Initial chromaticity	(0.38, 0.38) SDCM <3
		Power consumption tolerance	+/-10%
Operating and Electrical			
Input Voltage	220-240 V	Over Time Performance (IEC Compliant	)
Line Frequency	50 to 60 Hz	Control gear failure rate at median useful life	5 %
Average CLO power consumption	- W	50000 h	
Inrush current	5.1 A	Control gear failure rate at median useful life	10 %
Inrush time	76 ms	100000 h	
Power Consumption	156 W	Lumen maintenance at median useful life*	L90
Power Factor (Fraction)	0.9	50000 h	
Connection	External connector	Lumen maintenance at median useful life*	L80
Cable	Cord with plug Wieland/Adels	100000 h	
	compatible 5-pole		
Number of products on MCB of 16 A type B	12	Application Conditions	
		Performance ambient temperature Tq	45 °C
Temperature		Maximum dim level	10%
Ambient temperature range	-30 to +45 ℃	Suitable for random switching	No
Controls and Dimming		Product Data	
Dimmable	Yes	Order product name	BY481P LED250S/840 PSD MB GC WH
			BR
Driver/power unit/transformer  Control interface	Power supply unit with DALI interface	Full product name	BY481P LED250S/840 PSD MB GC WH
Control light output	DALI		BR
Constant light output	No	Full product code	871869940781000
Machanical and Housing		Order code	40781000
Mechanical and Housing	Aluminum	Material Nr. (12NC)	910500465587
Housing Material	Aluminum	Numerator - Quantity Per Pack	1
Reflector material	Polygarhonato	EAN/UPC - Product/Case	8718699407810
Optic material	Polycarbonate	Numerator - Packs per outer box	1
Optical cover material	Glass	EAN/UPC - Case	8718699407810
Fixation material	Steel		
Housing Color	White		

## **GentleSpace Gen3**

#### Dimensional drawing





