



TownGuide Performer

BDP100 LED60/740 II DW PCF SI LS-6 62P

TOWNGUIDE PERF FLAT CONE, LED module 6000 lm,
Distribution wide, Polycarbonate bowl/cover frosted, LumiStep
dimming 6 hours, Post-top for diameter 62 mm

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project’s specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

Product data

General Information		Service tag	
Lamp family code	LED60 [LED module 6000 lm]	Product family code	BDP100 [TOWNGUIDE PERF FLAT CONE]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Performance
Driver included	Yes	Embedded control	LumiStep dimming 6 hours
Photocell	-	CE mark	Yes
Light source engine type	LED	Warranty period	5 years

TownGuide Performer

Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	3
Luminous Flux	3,240 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	70
Number of light sources	4
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover frosted
Luminaire light beam spread	50° x 70°
Optic type outdoor	Distribution wide

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	39 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Mounting device	Post-top for diameter 62 mm

Optical cover shape	Conical flat
Optical cover finish	Frosted
Overall height	209 mm
Overall diameter	570 mm
Effective projected area	0.051 m²
Parts color	All parts colored

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	95

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	50%

Product Data

Order product name	BDP100 LED60/740 II DW PCF SI LS-6 62P
Full product name	BDP100 LED60/740 II DW PCF SI LS-6 62P
Full product code	871829191001500
Order code	910500991061
Material Nr. (12NC)	910500991061
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291910015
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291910015

TownGuide Performer

Dimensional drawing

