



SmartForm TBS415

TBS415 1x49W/830 HFP D8 W AIR

SmartForm recessed semi-modular, 1, 49 W, 830 warm white, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS415 – 'light beam' semi-modular – 600 mm module. SmartForm recessed luminaires are designed for integration in linear ceiling systems with a width of 148 mm (half module 300 mm) for exposed and concealed T-bar and the extended versions for bandraaster ceilings. 'Light surface' TBS415 1-lamp. MLO and asymmetrical optic in 1/2 modular concept, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 1-lamp: micro-optics in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 2-lamps. Mini-optics, 2-lamps in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm.

Product data

SmartForm TBS415

General Information

Lamp family code	TL5 [TL5]
Cap-Base	G5 [G5]
Gear	HFP [HF Performer]
Feed-through wiring	-
Product family code	TBS415 [SmartForm recessed semi-modular]
Lighting Technology	Fluorescent
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical

Number of light sources	1
Light source color	830 warm white
Optic type	Semi-high-gloss optic 3D micro-lamellae
Optical cover type	-

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	49 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Mechanical and Housing

Housing Material	Steel
------------------	-------

Reflector material	Aluminum
Optic material	Aluminum
Housing Color	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TBS415 1x49W/830 HFP D8 W AIR
Full product name	TBS415 1x49W/830 HFP D8 W AIR
Full product code	871794398895200
Order code	98895200
Material Nr. (12NC)	910501910703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943988952
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943988952

Dimensional drawing



