



# PowerBalance Tunable White, recessed

## RC464B LED80S/TWH PSD W30L120 VPC W

PowerBalance recessed Tuneable WH, LED Module, system flux 8000 lm, Tunable white, Power supply unit with DALI interface, Plug-in connector 3-pole Wieland/Adels compatible

The right light can have a favorable effect on various physiological processes in the human body. Statistically, 65% of office workers feel short of their best before 9.00 hours. By giving them personal control over the lighting in their work space, so they can tailor it to suit the time of day and what they are doing, our PowerBalance Tunable White solution can enhance their comfort, task performance, and productivity. Similarly, in schools, PowerBalance Tunable White allows teachers to create the right mood to help pupils to concentrate, relax, etc., depending on the activity at hand, and so perform better overall.

### Product data

| General Information      |  |
|--------------------------|--|
| Lamp family code         | LED80S [LED Module, system flux 8000 lm]                                     |
| Cap-Base                 | - [-]  |
| Light source replaceable | No   |
| Number of gear units     | 1 unit   |
| Gear                     | -  |
| Driver included          | Yes  |
| Remarks                  | *-Per Lighting Europe guidance paper<br>“Evaluating performance of LED based |

|                     |   |
|---------------------|---|
|                     | luminaire - January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. |
| Service tag         | Yes   |
| Product family code | RC464B [PowerBalance recessed Tuneable WH]  |
| Lighting Technology | LED   |

## PowerBalance Tunable White, recessed

|                   |   |
|-------------------|---|
| Embedded control  | -   |
| CE mark           | Yes   |
| Warranty period   | 3 years                                     |
| Flammability mark | For mounting on normally flammable surfaces |
| ENEC mark         | ENEC plus mark                              |
| Glow-wire test    | Temperature 850 °C, duration 5 s            |
| EU RoHS compliant | Yes   |

### Light Technical

|                                 |                          |
|---------------------------------|--------------------------|
| Luminous Flux                   | 8,000 lm                 |
| Luminous Efficacy (rated) (Nom) | 110 lm/W                 |
| Color rendering index (CRI)     | ≥80                      |
| Number of light sources         | 1                        |
| Beam angle of light source      | 120 degree(s)            |
| Light source color              | Tunable white            |
| Optic type                      | -                        |
| Optical cover type              | Polycarbonate bowl/cover |
| Luminaire light beam spread     | 86°                      |
| Unified glare rating CEN        | 19                       |

### Operating and Electrical

|  |   |
|--|---|
| Input Voltage                            | 220-240 V   |
| Line Frequency                           | 50 to 60 Hz                                       |
| Inrush current                           | 5 A   |
| Inrush time                              | 1 ms  |
| Power Consumption                        | 73 W  |
| Power Factor (Fraction)                  | 0.9   |
| Connection                               | Plug-in connector 3-pole Wieland/Adels compatible |
| Cable                                    | -   |
| Number of products on MCB of 16 A type B | 20  |

### Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | +10 to +40 °C |
|---------------------------|---------------|

### Controls and Dimming

|                               |                                       |
|-------------------------------|---------------------------------------|
| Dimmable                      | Yes                                   |
| Driver/power unit/transformer | Power supply unit with DALI interface |
| Control interface             | DALI                                  |
| Constant light output         | No                                    |

### Mechanical and Housing

|                  |                     |
|------------------|---------------------|
| Housing Material | Composite materials |
|------------------|---------------------|

|                                     |                    |
|-------------------------------------|--------------------|
| Reflector material                  | Polycarbonate      |
| Optic material                      | -                  |
| Optical cover material              | Polycarbonate      |
| Fixation material                   | -                  |
| Housing Color                       | White RAL 9003     |
| Optical cover finish                | Matte              |
| Overall length                      | 1,197 mm           |
| Overall width                       | 297 mm             |
| Overall height                      | 79 mm              |
| Dimensions (Height x Width x Depth) | 79 x 297 x 1197 mm |

### Approval and Application

|                              |                         |
|------------------------------|-------------------------|
| Ingress protection code      | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard]   |
| Protection class IEC         | Safety class I          |

### Initial Performance (IEC Compliant)

|                             |  |
|-----------------------------|--|
| Luminous flux tolerance     | +/-10%                                       |
| Initial chromaticity        | (0.31, 0.32) SDCM <3 to (0.43, 0.40) SDCM <3 |
| Power consumption tolerance | +/-10%                                       |

### Over Time Performance (IEC Compliant)

|   |     |
|---|-----|
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h        | L90 |

### Application Conditions

|                                    |       |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level                  | 1%    |
| Suitable for random switching      | No    |

### Product Data

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Order product name              | RC464B LED80S/TWH PSD W30L120 VPC W |
| Full product name               | RC464B LED80S/TWH PSD W30L120 VPC W |
| Full product code               | 871869687467700                     |
| Order code                      | 87467700                            |
| Material Nr. (12NC)             | 910502042803                        |
| Numerator - Quantity Per Pack   | 1                                   |
| EAN/UPC - Product/Case          | 8718696874677                       |
| Numerator - Packs per outer box | 1                                   |
| EAN/UPC - Case                  | 8718696874677                       |

## PowerBalance Tunable White, recessed

### Dimensional drawing

