



PowerBalance Tunable White, recessed

RC464B LED80S/TWH PSD W30L120 PCV PIP

PowerBalance Tunable White, recessed, 73 W, 8000 lm, DALI

The right light can have a favorable effect on various physiological processes in the human body. Statistically, 65% of office workers feel short of their best before 9.00 hours. By giving them personal control over the lighting in their work space, so they can tailor it to suit the time of day and what they are doing, our PowerBalance Tunable White solution can enhance their comfort, task performance, and productivity. Similarly, in schools, PowerBalance Tunable White allows teachers to create the right mood to help pupils to concentrate, relax, etc., depending on the activity at hand, and so perform better overall.

Product data

General Information			
Lamp family code	LED80S [LED Module, system flux 8000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Service tag	Yes
Light source replaceable	No	Product family code	RC464B [PowerBalance recessed Tuneable WH]
Number of gear units	1 unit	Lighting Technology	LED
Gear	-	Embedded control	-
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Warranty period	3 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC plus mark

PowerBalance Tunable White, recessed

Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	8,000 lm
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	Tunable white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	86°
Unified glare rating CEN	19

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	73 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Composite materials
Reflector material	Polycarbonate
Optic material	-
Optical cover material	Polycarbonate
Fixation material	-

Housing Color	White RAL 9003
Optical cover finish	Matte
Overall length	1,197 mm
Overall width	297 mm
Overall height	79 mm
Dimensions (Height x Width x Depth)	79 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.32) SDCM <3 to (0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	RC464B LED80S/TWH PSD W30L120 PCV PIP
Full product name	RC464B LED80S/TWH PSD W30L120 PCV PIP
Full product code	871869907169100
Order code	07169100
Material Nr. (12NC)	910502054703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699071691
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699071691

PowerBalance Tunable White, recessed

Dimensional drawing

