



Iridium SGS253/453

SGS253 SON-T150W K I OR PC GR SND

IRIDIUM, SON-T, 150 W, Open CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


Product data

General Information		Power Consumption	
Lamp family code	SON-T [SON-T]	150 W	
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Housing Color	
Product family code	SGS253 [IRIDIUM]	Grey	
Embedded control	-	Overall height	
CE mark	Yes	289 mm	
ENEC mark	ENEC mark	Parts color	
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	
Standard tilt angle side entry	5°	IP66 [Dust penetration-protected, jet-proof]	
Number of light sources	1	Mech. impact protection code	
Optical cover type	Polycarbonate bowl/cover	IK08 [5 J vandal-protected]	
Optic type outdoor	Open CT-POT	Protection class IEC	
Operating and Electrical		Safety class I	
Input Voltage	230 V	Product Data	
		Order product name	
		SGS253 SON-T150W K I OR PC GR SND	
		Full product name	
		SGS253 SON-T150W K I OR PC GR SND	
		Full product code	
		871155984456500	
		Order code	
		84456500	
		Material Nr. (12NC)	
		910502133818	
		Numerator - Quantity Per Pack	
		1	

Iridium SGS253/453

EAN/UPC - Product/Case	8711559844565
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559844565

Dimensional drawing



Product	A
SGS253 SON-T150W K I OR PC GR SND	289 mm

