



LuxSpace Mini, recessed

DN560B LED12S/830 PSE-E F PG WH

LuxSpace2 Mini Low height recessed, LED module, system flux 1200 lm, 830 warm white, Power supply unit DC compatible, external, Facetted reflector, Protection glass, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is.

Product data

General Information		Service tag	Yes
Lamp family code	LED12S [LED module, system flux 1200 lm]	Product family code	DN560B [LuxSpace2 Mini Low height recessed]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	No

LuxSpace Mini, recessed

Light Technical	
Luminous Flux	1,150 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	99 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optic type	Facetted reflector
Optical cover type	Protection glass
Luminaire light beam spread	80°
Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	11.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

Temperature	
Ambient temperature range	+10 to +25 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel

Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	72 mm
Overall diameter	164 mm

Approval and Application	
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data	
Order product name	DN560B LED12S/830 PSE-E F PG WH
Full product name	DN560B LED12S/830 PSE-E F PG WH
Full product code	871829193651000
Order code	910503586430
Material Nr. (12NC)	910503586430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291936510
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291936510

Dimensional drawing



LuxSpace Mini, recessed

