



# LuxSpace, recessed

## DN570B LED12S/830 PSD-VLC-E WR WH

LUXSPACE 2 COMPACT LOW HEIGHT, LED module, system flux 1200 lm, 830 warm white, Power supply unit with DALI interface, DC compatible, external, White reflector without louver, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is. For office applications LuxSpace supports health and wellbeing having dedicated Tunable White products and lighting controls.

### Product data

General Information			
Lamp family code	LED12S [LED module, system flux 1200 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	DN570B [LUXSPACE 2 COMPACT LOW HEIGHT]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s

## LuxSpace, recessed

EU RoHS compliant	No
-------------------	----

### Light Technical

Luminous Flux	1,300 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optic type	White reflector without louver
Optical cover type	-
Luminaire light beam spread	80°
Unified glare rating CEN	22

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	11 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Fixation material	Steel
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	96.5 mm
Overall diameter	214 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	DN570B LED12S/830 PSD-VLC-E WR WH
Full product name	DN570B LED12S/830 PSD-VLC-E WR WH
Full product code	871829193051800
Order code	910503587515
Material Nr. (12NC)	910503587515
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291930518
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291930518

## LuxSpace, recessed

### Dimensional drawing

