



# LuxSpace, recessed

## DN570B LED20S/840 PSU-E F WH

LUXSPACE 2 COMPACT LOW HEIGHT - LED Module, system flux 2000 lm - 840 neutral white - Power supply unit DC compatible, external - Facetted reflector - White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application. For office applications LuxSpace supports the general feeling of health and wellbeing having dedicated Tunable White products

### Product data

General Information			
Number of light sources	1 pc	Luminaire light beam spread	80°
Lamp family code	LED20S [ LED Module, system flux 2000 lm]	Emergency lighting	-
Light source color	840 neutral white	Connection	Push-in connector and pull relief
Cap-Base	- [ -]	Cable	-
Light source replaceable	No	Protection class IEC	Safety class II
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 5 s
Gear	-	Flammability mark	For mounting on normally flammable surfaces
Driver/power unit/transformer	Power supply unit DC compatible, external	CE mark	CE mark
Driver included	Yes	ENEC mark	ENEC mark
Optic type	Facetted reflector	UL mark	-
Optical cover/lens type	-	Warranty period	5 years

## LuxSpace, recessed

Decorative accessories	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	32
EU RoHS compliant	No
Product family code	DN570B [ LUXSPACE 2 COMPACT LOW HEIGHT]
Unified glare rating CEN	22

### Light Technical

Optical cover/lens type accessory	-
-----------------------------------	---

### Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Factor (Min)	0.9

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Housing configuration	Basic version
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	96,5 mm
Overall diameter	214 mm
Color	White RAL 9003

Dimensions (Height x Width x Depth)	97 x NaN x NaN mm (3.8 x NaN x NaN in)
-------------------------------------	--

### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	2200 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	126 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.38, 0.37) SDCM <3
Initial input power	17.4 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

### Application Conditions


Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Full product code	871829193057000
Order product name	DN570B LED20S/840 PSU-E F WH
EAN/UPC - Product	8718291930570
Order code	910503588115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503588115
Net Weight (Piece)	1.150 kg




Dimensional drawing




LuxSpace gen2 DN570B-DN572B

Photometric data

DN570B PSE-E 1xLED20S/840 F



DN570B PSE-E 1xLED20S/840 F



IFGU\_DN570B PSE-E 1xLED20S/840 F-General uniform lighting

IFPC\_DN570B PSE-E 1xLED20S/840 F-Polar Indoor (combined)

