



# LuxSpace, recessed

#### DN570B LED20S/830 PSU-E WR WH

LUXSPACE 2 COMPACT LOW HEIGHT, LED Module, system flux 2000 lm, 830 warm white, Power supply unit DC-compatible, external, White reflector without louvre, White RAL 9003

Customers are looking to optimise all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (colour rendering and colour uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

#### **Product data**

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen
	maintenance between the B50 and, for
	example, the B10. Therefore, the median

	useful life (B50) value also represents the B10
	value.
Product family code	DN570B [LUXSPACE 2 COMPACT LOW
	HEIGHT]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable
	surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	No


Datasheet, 2023, December 5 data subject to change


## LuxSpace, recessed

Light Technical	
Luminous Flux	2,100 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	111 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optic type	White reflector without louvre
Optical cover type	-
Luminaire light beam spread	80°
Unified Glare Rating (CEN)	25
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	19 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type	32
В	
Temperature	
Ambient temperature range	+10 to +25 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit DC-compatible, external
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White RAL 9003

Optical cover/lens finish	Frosted
Overall height	96.5 mm
Overall diameter	214 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM≤2
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compl	iant)
Control gear failure rate at median useful	5 %
life 50,000 h	
Lumen maintenance at median useful	L90
life* 50,000 h	
Lumen maintenance at median useful	L80
life* 100,000 h	
Application Conditions	
Performance ambient temperature Tq	25 ℃
Suitable for random switching	Yes
Duradicat Data	
Product Data	DNEZOD I ED300 (030 DCI I E WD ) ""
Order product name	DN570B LED20S/830 PSU-E WR WH
Full product name	DN570B LED20S/830 PSU-E WR WH
Full EOC	871829193062400
Order code  Material no. (12 NC)	93062400
Material no. (12 NC)	910503588615
SAP numerator – quantity per pack	0710201020524
EAN/UPC — Product/Case	8718291930624
Numerator – packs per outer box	0710201020524
EAN/UPC - Case	8718291930624

## Dimensional drawing





#### LuxSpace, recessed



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.