



# LuxSpace, recessed

## DN570B LED20S/830 PSU-E C WH SG-FRC

LUXSPACE 2 COMPACT LOW HEIGHT, LED Module, system flux 2000 lm, 830 warm white, Power supply unit DC-compatible, external, High-gloss mirror, White RAL 9003

Customers are looking to optimise all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (colour rendering and colour uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code	DN570B [LUXSPACE 2 COMPACT LOW HEIGHT]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	No

## LuxSpace, recessed

### Light Technical

Luminous Flux	1,800 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	95 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optic type	High-gloss mirror
Optical cover type	-
Luminaire light beam spread	80°
Unified Glare Rating (CEN)	25

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	19 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

### Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC-compatible, external
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White RAL 9003

Optical cover/lens finish	Frosted
Overall height	96.5 mm
Overall diameter	214 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80


### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Order product name	DN570B LED20S/830 PSU-E C WH SG-FRC
Full product name	DN570B LED20S/830 PSU-E C WH SG-FRC
Full EOC	871829193103400
Order code	93103400
Material no. (12 NC)	910503592715
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291931034
Numerator – packs per outer box	1
EAN/UPC - Case	8718291931034

## Dimensional drawing



LuxSpace, recessed

