PHILIPS Lighting



LuxSpace, recessed

DN571B LED24S/830 PSE-E C WH

LUXSPACE 2 COMPACT DEEP, LED module, system flux 2400 lm, 830 warm white, Power supply unit DC-compatible, external, High-gloss mirror, White RAL 9003

Customers are looking to optimise all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (colour rendering and colour uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Product data

General Information	
Lamp family code	LED24S [LED module, system flux 2400 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen
	maintenance between the B50 and, for
	example, the B10. Therefore, the median

	useful life (B50) value also represents the
	B10 value.
Product family code	DN571B [LUXSPACE 2 COMPACT DEEP]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable
	surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	No

LuxSpace, recessed

Light Technical	
Luminous Flux	2,500 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	109 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optic type	High-gloss mirror
Optical cover type	-
Luminaire light beam spread	70°
Unified Glare Rating (CEN)	19

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	23 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type	32
В	

Temperature

Ambient temperature range	+10 to +25 °C	
Controls and Dimming		
Dimmable	No	

Dimmable	No
Driver/power unit/transformer	Power supply unit DC-compatible, external
Constant light output	No


Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White RAL 9003

Optical cover/lens finish	Frosted
Overall height	119 mm
Overall diameter	214 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant	•)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%
	,
Over Time Performance (IEC Comp	liant)
Control gear failure rate at median usefu	ıl 5%
life 50,000 h	
Lumen maintenance at median useful	L90
life* 50,000 h	
Lumen maintenance at median useful	L80
life* 100,000 h	
Application Conditions	
Performance ambient temperature Tg	25 °C
Suitable for random switching	Yes
Product Data	
Order product name	DN571B LED24S/830 PSE-E C WH
Full product name	DN571B LED24S/830 PSE-E C WH
Full EOC	871829193145400
Order code	93145400

Full product name DNS/IB LED245/830 PSE-E C WH Full EOC 871829193145400 Order code 93145400 Material no. (12 NC) 910503596915 SAP numerator – quantity per pack 1 EAN/UPC – Product/Case 8718291931454 Numerator – packs per outer box 1 EAN/UPC - Case 8718291931454

Dimensional drawing



LuxSpace, recessed



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, December 5 - data subject to change