



# TCW060

## TCW060 2xTL-D36W HF

2 pcs - MASTER TL-D - 36 W - Electronic high-frequency


Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

### Product data

General Information	
Number of light sources	2 [ 2 pcs]
Lamp family code	TL-D [ MASTER TL-D]
Lamp power	36 W
Kombipack	-
Gear	HF [ Electronic high-frequency]
Optical cover/lens type	PCP [ Polycarbonate bowl/cover prismatic]
Emergency lighting	No [ -]
Connection	SI [ Screw connection block]
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Country version	NO [ Norway]
CE mark	CE mark
Operating and Electrical	
Input voltage	220 to 240 V
Mechanical and Housing	
Fixation point length distance (nom.)	900 mm
Overall length	1270 mm



Colour	Grey
Dimensions (height x width x depth)	NaN x NaN x 1270 mm (NaN x NaN x 50 in)
Approval and Application	
Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Application Conditions	
Suitable for random switching	No
Product Data	
Full product code	871155981380699
Order product name	TCW060 2xTL-D36W HF
EAN/UPC – product	8711559813806
Order code	81380699
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	910503610918
Net weight (piece)	2.650 kg

Dimensional drawing



TCW060

Photometric data



IFGU\_TCW060 2xTL-D36W HF-General uniform lighting

IFPC\_TCW060 2xTL-D36W HF-Polar Indoor (combined)

