



LuxSpace Mini, recessed

DN560B LED8S/840 PSED-VLC-E C WH

LuxSpace2 Mini Low height recessed - LED Module, system flux 800 lm - 840 neutral white - Power supply unit with DALI interface, DC-compatible, external - High-gloss mirror - White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Product data

General Information		Driver included	Yes
Number of light sources	1 pc	Optic type	High-gloss mirror
Lamp family code	LED8S [LED Module, system flux 800 lm]	Optical cover/lens type	-
Light source color	840 neutral white	Luminaire light beam spread	80°
Cap-Base	- [-]	Emergency lighting	-
Light source replaceable	No	Control interface	DALI
Number of gear units	1 unit	Connection	Push-in connector and pull relief
Gear	-	Cable	-
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external	Protection class IEC	Safety class II
		Glow-wire test	Temperature 850 °C, duration 5 s

LuxSpace Mini, recessed

Flammability mark	For mounting on normally flammable surfaces
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Decorative accessories	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	50
RoHS mark	-
Product family code	DN560B [LuxSpace2 Mini Low height recessed]
Unified glare rating CEN	22

Light Technical

Optical cover/lens type accessory -

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	0.05 ms
Power Factor (Min)	0.8

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Housing configuration	-
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted

Overall height	72 mm
Overall diameter	164 mm
Color	White RAL 9003

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	820 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	103 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.38, 0.37) SDCM <3
Initial input power	8 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions


Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Full product code	871829193763000
Order product name	DN560B LED8S/840 PSED-VLC-E C WH
EAN/UPC - Product	8718291937630
Order code	910503706509
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503706509
Net Weight (Piece)	0.720 kg

LuxSpace Mini, recessed

Dimensional drawing



LuxSpace gen2 Mini DN560B-DN561C

