



# LuxSpace Mini, recessed

## DN561B LED8S/840 PSD-VLC-E C WH

LuxSpace2 Mini Deep recessed, LED Module, system flux 800 lm, 840 neutral white, Power supply unit with DALI interface, DC compatible, external, High-gloss mirror, White

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is.

### Product data

General Information		Product family code	
Lamp family code	LED8S [LED Module, system flux 800 lm]	Product family code	DN561B [LuxSpace2 Mini Deep recessed]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	No
		Light Technical	
		Luminous Flux	780 lm

LuxSpace Mini, recessed

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	98 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	840 neutral white
Optic type	High-gloss mirror
Optical cover type	-
Luminaire light beam spread	75°
Unified glare rating CEN	19

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	0.05 ms
Power Consumption	8 W
Power Factor (Fraction)	0.8
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	50

Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel

Housing Color	White
Optical cover finish	Frosted
Overall height	86 mm
Overall diameter	164 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN561B LED8S/840 PSD-VLC-E C WH
Full product name	DN561B LED8S/840 PSD-VLC-E C WH
Full product code	871829193771500
Order code	910503706517
Material Nr. (12NC)	910503706517
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291937715
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291937715

Dimensional drawing



## LuxSpace Mini, recessed

