



LuxSpace PoE

DN570B LED20S/830 POE F WH

LuxSpace PoE, 15.4 W, 2200 lm, 3000 K, Power over Ethernet, Frosted

With Power-over-Ethernet (PoE) technology, LuxSpace PoE receives power and data over a single standard Ethernet cable, eliminating the need for separate power cabling. With the simple click of a connector, LuxSpace PoE luminaires become part of a complete, integrated connected lighting system, delivering extraordinary illumination experiences and value beyond illumination. A built-in lighting and control system gives office users personal control over their preferred light settings via a specially designed smartphone app. With integrated sensors, LuxSpace PoE luminaires can track activity patterns, daylight levels, and in the near future humidity, CO₂, temperature, or other data. This data allows facility managers to gain deep insight into building operations, helping them optimize the delivery of resources, enhance the experience and performance of occupants, and support improved asset management.

Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	DN570B [LUXSPACE 2 COMPACT LOW HEIGHT]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 5 s
Gear	-	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	No

LuxSpace PoE

Value ladder	Specification
Light Technical	
Luminous Flux	2,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	143 lm/W
Color rendering index (CRI)	>80
Light source color	830 warm white
Optic type	Facetted reflector
Luminaire light beam spread	80°
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	48 to 54 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	15.4 W
Power Factor (Fraction)	1
Connection	RJ45 connector
Cable	-
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	+10 to +25 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Luminaire controller with power over Ethernet
Control interface	Power over Ethernet
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Fixation material	Steel
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	96.5 mm
Overall diameter	214 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes
Product Data	
Order product name	DN570B LED20S/830 POE F WH
Full product name	DN570B LED20S/830 POE F WH
Full product code	871829194352500
Order code	910503706665
Material Nr. (12NC)	910503706665
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291943525
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291943525

Dimensional drawing

