



# LuxSpace PoE

## DN560B LED12S/840 POE F WH

LuxSpace PoE, 8.7 W, 1200 lm, 4000 K, Power over Ethernet, Frosted

With Power-over-Ethernet (PoE) technology, LuxSpace PoE receives power and data over a single standard Ethernet cable, eliminating the need for separate power cabling. With the simple click of a connector, LuxSpace PoE luminaires become part of a complete, integrated connected lighting system, delivering extraordinary illumination experiences and value beyond illumination. A built-in lighting and control system gives office users personal control over their preferred light settings via a specially designed smartphone app. With integrated sensors, LuxSpace PoE luminaires can track activity patterns, daylight levels, and in the near future humidity, CO2, temperature, or other data. This data allows facility managers to gain deep insight into building operations, helping them optimize the delivery of resources, enhance the experience and performance of occupants, and support improved asset management.

### Product data

General Information			
Lamp family code	LED12S [LED module, system flux 1200 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	DN560B [LuxSpace2 Mini Low height recessed]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 5 s
Gear	-	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	No

Value ladder	Specification
<b>Light Technical</b>	
Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Facetted reflector
Luminaire light beam spread	80°
Unified glare rating CEN	22
<b>Operating and Electrical</b>	
Input Voltage	48 to 54 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	8.7 W
Power Factor (Fraction)	1
Connection	RJ45 connector
Cable	-
Number of products on MCB of 16 A type B	-
<b>Temperature</b>	
Ambient temperature range	+10 to +25 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Luminaire controller with power over Ethernet
Control interface	Power over Ethernet
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Fixation material	Steel
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	72 mm
Overall diameter	164 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	DN560B LED12S/840 POE F WH
Full product name	DN560B LED12S/840 POE F WH
Full product code	871829194359400
Order code	910503706672
Material Nr. (12NC)	910503706672
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291943594
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291943594

## Dimensional drawing

