



# LuxSpace, recessed

## DN571B LED20S/830 PSD-VLC-E C ELP3 WH

LuxSpace, recessed, 22 W, 2100 lm, 3000 K, DALI, Frosted

Customers are looking to optimise all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (colour rendering and colour uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	DN571B [LUXSPACE 2 COMPACT DEEP]
Lighting Technology	LED


Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Luminous Flux	2,100 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	95 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optic type	High-gloss mirror
Luminaire light beam spread	70°

LuxSpace, recessed

Unified Glare Rating (CEN)	19
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	+10 to +25 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White RAL 9003
Optical cover/lens finish	Frosted
Overall height	119 mm
Overall diameter	214 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1% (no dimming in emergency mode)
Suitable for random switching	Yes
Product Data	
Order product name	DN571B LED20S/830 PSD-VLC-E C ELP3 WH
Full product name	DN571B LED20S/830 PSD-VLC-E C ELP3 WH
Full EOC	871829194383900
Order code	94383900
Material no. (12 NC)	910503706695
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291943839
Numerator – packs per outer box	1
EAN/UPC – Case	8718291943839

Dimensional drawing



LuxSpace, recessed

