



LuxSpace, surface mounted

DN570C LED20S/840 PSD-VLC-E C WH

LuxSpace, surface mounted, 17.4 W, 2200 lm, 4000 K, DALI, Frosted

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Service tag	Yes
Light source replaceable	No	Product family code	DN570C [LUXSPACE 2 COMPACT LOW HEIGHT]
Number of gear units	1 unit	Lighting Technology	LED
Gear	-	Value ladder	Specification
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s

LuxSpace, surface mounted

EU RoHS compliant	No
-------------------	----

Light Technical

Luminous Flux	2,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	126 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	80°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 Hz
Inrush current	16 A
Inrush time	0.220 ms
Power Consumption	17.4 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Fixation material	Steel
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	217 mm
Overall diameter	250 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN570C LED20S/840 PSD-VLC-E C WH
Full product name	DN570C LED20S/840 PSD-VLC-E C WH
Full product code	871829194487400
Order code	910503706712
Material Nr. (12NC)	910503706712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291944874
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291944874

LuxSpace, surface mounted

Dimensional drawing

