



Pentura Mini LED

BN132C LED3S/830 PSU L300

LED Medium Power, 830 warm white, Power supply unit (On/Off)

Pentura Mini LED is an extremely slim batten that offers the energy-saving benefits of LED technology, coupled with excellent lighting performance – bright, uniform light with good color rendering. Pentura Mini LED is very easy to install, even where space is limited, e.g. under shelves in shops, and over worktops and workstations in the home and home office. Thanks to its integrated driver and through-wiring, installation time is reduced to a minimum. Power cable, mounting clips and connection accessories are also supplied. Thin end-caps minimize black spots between the products, enabling consumers to create a continuous light-line.

Product data


General Information		Warranty period	
Lamp family code	LED-MP [LED Medium Power]	Flammability mark	-
Light source replaceable	No	ENEC mark	-
Number of gear units	Unit	Glow-wire test	Temperature 650 °C, duration 30 s
Gear	-	EU RoHS compliant	Yes
Driver included	Yes	Light Technical	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Luminous Flux	350 lm
Lighting Technology	LED	Correlated Colour Temperature	3000 K
CE mark	Yes	Luminous efficacy (rated) (nom.)	88 lm/W
		Colour rendering index (CRI)	≥80
		Beam angle of light source	- degree(s)
		Light source colour	830 warm white
		Optic type	-

Pentura Mini LED

Luminaire light beam spread	135°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	2 A
Inrush time	3.2 ms
Power Consumption	4 W
Power Factor (Fraction)	0.8
Connection	Flying leads/cables
Cable	-
Number of products on MCB of 16 A type B	180
Temperature	
Ambient temperature range	0 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	-
Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	338 mm
Overall width	22 mm
Overall height	34 mm
Dimensions (height x width x depth)	34 x 22 x 338 mm

Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.41) SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance at median useful life* 50,000 h	L65
Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	No
Product Data	
Order product name	BN132C LED3S/830 PSU L300
Full product name	BN132C LED3S/830 PSU L300
Full EOC	871869607250999
Order code	07250999
Material no. (12 NC)	910503910163
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696072509
Numerator – packs per outer box	24
EAN/UPC - Case	8718696072608

Dimensional drawing



Pentura Mini LED

