



# Ledinaire recessed

## RC060B LED32S/840 PSU W60L60

Ledinaire recessed, 36 W, 600x600 mm, 3200 lm, 4000 K

Uncomplicated, off-the-shelf quality and reliability – that’s the beauty of LEDINAIRE. LEDINAIRE keeps it simple, delivering the essentials and nothing more. We don’t spend money on things you don’t need: no flashy packaging, no unnecessary brochures. We offer a selection of popular, low-cost LED solutions, ensuring that LED lighting is within your price range, and that our products always meet the highest possible standard. This no-nonsense approach to lighting means that you get exactly what it says on the box – reliability, affordability, and energy efficiency. Designed for general lighting, LEDINAIRE RC060B Recessed is a cost-effective, energy-saving LED solution for application in offices, classrooms, corridors and circulation areas.

### Product data

General Information	
Cap-Base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Lighting Technology	LED
Value ladder	Value

CE mark	Yes
Warranty period	2 years
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	3,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	≥80
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	108°

## Ledinaire recessed

Unified glare rating CEN	22
--------------------------	----

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	5.3 A
Inrush time	7 ms
Power Consumption	36 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	597 mm
Overall width	597 mm
Overall height	41 mm
Dimensions (Height x Width x Depth)	41 x 597 x 597 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	7.5 %
Lumen maintenance at median useful life* L70	50000 h


### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

### Product Data

Order product name	RC060B LED32S/840 PSU W60L60
Full product name	RC060B LED32S/840 PSU W60L60
Full product code	871869606958500
Order code	06958500
Material Nr. (12NC)	910503910201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696069585
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696069585

## Dimensional drawing



## Ledinaire recessed

