



CoreLine Batten

BN124C LED41S/840 PSU TW1 L1200

CoreLine Batten, 38 W, L1200 mm, 4100 lm, 4000 K, Frosted, IP20, TW1

The CoreLine Batten delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. The efficient design makes installation quick and easy, enabling seamless light-line creation without additional accessories. CoreLine Batten provides universal light distribution, supporting homogeneous illuminance and visual comfort. Interact Ready luminaires with integrated wireless communications are also available, for use with Interact gateways, sensors and software.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Lamp family code	LED41S [LED module, system flux 4100 lm]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Feed-through wiring	Feed-through wiring 1-phase
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example

Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easy flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 850 °C, duration 30 s

CoreLine Batten

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	108 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	120°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
End CLO power consumption	- W
Inrush current	0.29 A
Inrush time	0.06 ms
Power Consumption	38 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White

Optical cover finish	Frosted
Overall length	1,135 mm
Overall width	64 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 64 x 1135 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDC M<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	BN124C LED41S/840 PSU TW1 L1200
Full product name	BN124C LED41S/840 PSU TW1 L1200
Full product code	871869607474999
Order code	910503910279
Material Nr. (12NC)	910503910279
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696074749
Numerator - Packs per outer box	8
EAN/UPC - Case	8718699380052

CoreLine Batten

Dimensional drawing

