PHILIPS Lighting



Iridium LED Mini

BGS451 GRN29--3S/740 I MSO GR P3

Mini Iridium LED, LED GreenLine 2900 lm, Medium wide street optic, Minicell (hole 20 mm)

The second generation of compact Mini Iridium LED road-lighting luminaires offers a much wider scope of application thanks to a more powerful LED engine and brand new optics, which allow maximum energy savings in residential streets. Additional control devices can be fitted into the mast and communicate with the luminaire to further increase energy savings. This new generation of Mini Iridium LED also gives municipal authorities the freedom to change the atmosphere of the street thanks to the choice of different color temperatures (warm, neutral and cool white).

Product data

General Information	
Lamp family code	GRN29 [LED GreenLine 2900 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Photocell	Minicell (hole 20 mm)
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value.
Light source engine type	LED
Product family code	BGS451 [Mini Iridium LED]
Lighting Technology	LED

Glow-wire test	Temperature 650 °C, duration 5 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0.03
Luminous Flux	2,905 lm
Standard tilt angle posttop	10°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	126 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white

Iridium LED Mini

Optical cover type	Polycarbonate bowl/cover	Eff
Luminaire light beam spread	180°	Dir
Optic type outdoor	Medium wide street optic	
		Ар
Operating and Electrical		Ing
Input Voltage	220 to 240 V	Me
Line Frequency	50 to 60 Hz	Sui
Inrush current	22 A	
Inrush time	0.29 ms	Pro
Power Consumption	23 W	
Power Factor (Fraction)	0.95	Ini
Connection	Internal connector	Lui
Cable	-	Ini
Number of products on MCB of 16 A type	20	Po
В		Ini
Temperature		0\
Ambient temperature range	-20 to +35 °C	Co
		life
Controls and Dimming		Lu
Dimmable	No	life
Driver/power unit/transformer	Power supply unit regulating	
Constant light output	No	Ap
		Pe
Mechanical and Housing		
Housing Material	Aluminum	Pr
Reflector material	-	Or
Optic material	Polycarbonate	Fu
Optical cover material	Polycarbonate	Fu
Fixation material	Aluminum	Or
Housing Color	Grey	Ma
Mounting device	Post-top for diameter 60 to 76 mm	Nu
Optical cover shape	Convex lens	EA
Optical cover finish	Clear	Nu
Overall length	529 mm	EA
Overall width	265 mm	
Overall height	154.5 mm	

Effective projected area	0.032 m²
Dimensions (Height x Width x Depth)	155 x 265 x 529 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV
	differential mode and 8 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.37) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Comp	liant)
Control gear failure rate at median usefu	l 10 %
life 100000 h	
Lumen maintenance at median useful	L80
life* 100000 h	
Application Conditions	
Performance ambient temperature Tq	25 °C
Product Data	
Order product name	BGS451 GRN293S/740 I MSO GR P3
Full product name	BGS451 GRN293S/740 I MSO GR P3
Full product code	871794385064800
Order code	910504998118
Material Nr. (12NC)	910504998118
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943850648
Numerator - Packs per outer box	1

Dimensional drawing



80

Iridium LED Mini



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change