



# CoreLine Waterproof

## WT120C G2 LED27S/840 PSU TW3 L1200

CoreLine Waterproof, 21.5 W, L1200 mm, 2700 lm, 4000 K, Wide beam, Frosted, IP65, IK08, TW3

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Lighting Technology	
Lamp family code	LED27S [LED Module, system flux 2700 lm]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Performance
Number of gear units	1 unit	CE mark	CE mark
Driver included	Yes	Warranty period	5 years
Feed-through wiring	Feed-through wiring 3-phase	Flammability mark	For mounting on easily flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Service tag	Yes	Glow-wire test	Temperature 850 °C, duration 30 s
Product family code	WT130C [Coreline Waterproof G2 LSC]	EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	2,700 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	126 lm/W
		Color rendering index (CRI)	>80

# CoreLine Waterproof

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	105°
Unified glare rating CEN	25

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	3.58 A
Inrush time	0.04 ms
Power Consumption	21.5 W
Power Factor (Fraction)	0.77
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	80

## Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray
Optical cover finish	Frosted
Overall length	1,215 mm
Overall width	80 mm
Overall height	76 mm

Dimensions (Height x Width x Depth)	76 x 80 x 1215 mm
-------------------------------------	-------------------

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	85
Lumen maintenance at median useful life* 100000 h	70

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

## Product Data

Order product name	WT120C G2 LED27S/840 PSU TW3 L1200
Full product name	WT120C G2 LED27S/840 PSU TW3 L1200
Full product code	871869691685800
Order code	91685800
Material Nr. (12NC)	910505100039
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696916858
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696916858

# CoreLine Waterproof

## Dimensional drawing

