



CoreLine Waterproof

WT120C G2 LED80S/840 PSU TW3 L1500

CoreLine Waterproof, 60 W, L1500 mm, 8000 lm, 4000 K, Wide beam, Frosted, IP65, IK08, TW3

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. With its slim and stylish design, it retains the product architecture that the range is well-known and appreciated for. Installation is quick and easy, all thanks to its efficient design. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. A direct replacement for traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W, it delivers significant energy savings. Interact Ready luminaires with integrated wireless communications are also available in the CoreLine waterproof range, ready to be used with Interact connected lighting system.

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information			
Lamp family code	LED80S [LED Module, system flux 8000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Service tag	Yes
Number of gear units	1 unit	Product family code	WT130C [Coreline Waterproof G2 LSC]
Driver included	Yes	Lighting Technology	LED
Feed-through wiring	Feed-through wiring 3-phase	Value ladder	Performance
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	CE mark	CE mark
		Warranty period	5 years
		Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 30 s

CoreLine Waterproof

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	8,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value 1 as per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	1.6
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	105°
Unified glare rating CEN	25

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	6.9 A
Inrush time	0.058 ms
Power Consumption	60 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	31

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray
Optical cover finish	Frosted

Overall length	1,515 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 1515 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	80
Lumen maintenance at median useful life* 100000 h	70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Product Data

Order product name	WT120C G2 LED80S/840 PSU TW3 L1500
Full product name	WT120C G2 LED80S/840 PSU TW3 L1500
Full product code	871869940930200
Order code	910505100077
Material Nr. (12NC)	910505100077
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699409302
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699409302

CoreLine Waterproof

Dimensional drawing

