



# TrueLine, suspended

## SP532P LED36S/940 PSD PI5 SM2 L1130 ALU

TrueLine DIRECT/INDIRECT OC, LED module, system flux 3600 lm, 940 neutral white, Power supply unit with DALI interface, Push-in connector 5-pole, Aluminum

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

### Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

General Information			
Lamp family code	LED36S [LED module, system flux 3600 lm]	Light source replaceable	No
		Number of gear units	1 unit
		Gear	GRT [Gear tray (without gear)]

## TrueLine, suspended

Driver included	Yes
Service tag	Yes
Product family code	SP532P [TrueLine DIRECT/INDIRECT OC]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	3,600 lm
Saturated Red (R9)	>50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	147 lm/W
Color rendering index (CRI)	>90
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4
Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	940 neutral white
Optic type	-
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	80°
Unified glare rating CEN	16

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	24.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	Cable 1.5 m with push-in connector 5-pole
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Aluminum
Optical cover finish	Frosted
Overall length	1,130 mm
Overall width	55 mm
Overall height	88 mm
Dimensions (Height x Width x Depth)	88 x 55 x 1130 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
Control gear failure rate at median useful life 5 % 50000 h	
Lumen maintenance at median useful life* 50000 h	L90

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

### Product Data

Order product name	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU
Full product name	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU
Full product code	871869996310100
Order code	910505100103
Material Nr. (12NC)	910505100103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699963101
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699963101

## TrueLine, suspended

### Dimensional drawing

