## **PHILIPS** Lighting



### Maxos LED inserts for TTX400

#### 4MX400 581 LED55S/830 PSD DA20 WH

Maxos LED Retrofit for TTX400, LED Module, system flux 5500 lm, 830 warm white, Power supply unit with DALI interface, Double asymmetric optic 20°, White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

#### **Product data**

# General Information Lamp family code LED55S [LED Module, system flux 5500 lm] Light source replaceable No Number of gear units 1 unit Gear Driver included Yes Remarks \*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically

	there is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value.
Service tag	Yes
Product family code	4MX400 [Maxos LED Retrofit for TTX400]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes

#### Maxos LED inserts for TTX400

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
•	
Light Technical	
Luminous Flux	5,500 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	169 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Double asymmetric optic 20°
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	20°
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	32.5 W
Power Factor (Fraction)	0.97
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A typ	<b>B</b> 24
Temperature	
Ambient temperature range	-20 to +35 °C
Controls and Dimming	
Controls and Dimming Dimmable	Yes
Dimmable	Yes Power supply unit with DALI interface DALI

Constant light output	No	
Mechanical and Housing		
Housing Material	Steel	
Reflector material	-	
Optic material	Polymethyl methacrylate	
Optical cover material	Polymethyl methacrylate	
Fixation material	Steel	

Housing Color	White
Optical cover finish	Clear
Overall length	1,528 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 63 x 1528 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

I = I = I = I = I = I = I = I = I	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3.5
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant) Control gear failure rate at median useful 5%

life 50000 h	
Control gear failure rate at median useful	10 %
life 100000 h	
Lumen maintenance at median useful life*	L90
50000 h	
Lumen maintenance at median useful life*	L80
100000 h	
A 10 10 M 100	

#### Application Conditions


Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

#### Product Data

Order product name	4MX400 581 LED55S/830 PSD DA20 WH
Full product name	4MX400 581 LED55S/830 PSD DA20 WH
Full product code	403073266323199
Order code	66323199
Material Nr. (12NC)	910629128826
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732663231
Numerator - Packs per outer box	3
EAN/UPC - Case	4030732260614

#### Maxos LED inserts for TTX400

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, August 31 - data subject to change